

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579919

Luminaire Tested: **HCC4S15D010BZ-HM40525930-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010BZ-HM40525930-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1366.0 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579919
CATALOG NUMBER: HCC4S15D010BZ-HM40525930-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P579919
 CATALOG NUMBER: HCC4S15D010BZ-HM40525930-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112158
5°	112686
10°	113450
15°	114582
20°	112675
25°	107503
30°	97662
35°	78767
40°	54665
45°	35882
50°	24044
55°	17118
60°	14604
65°	16782
70°	17996
75°	17347
80°	15698
85°	14294



TEST NUMBER: P579919
 CATALOG NUMBER: HCC4S15D010BZ-HM40525930-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	6.3
10°-20°	252.1	18.5
20°-30°	360.2	26.4
30°-40°	321.7	23.6
40°-50°	165.0	12.1
50°-60°	75.0	5.5
60°-70°	55.9	4.1
70°-80°	38.1	2.8
80°-90°	11.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.0	51.2
0°-40°	1020.7	74.7
0°-60°	1260.8	92.3
0°-90°	1366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1366.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	909	
5°	910	87
15°	897	252
25°	790	360
35°	523	322
45°	206	165
55°	80	75
65°	58	56
75°	36	38
85°	10	11
90°	0	



TEST NUMBER: P579919
CATALOG NUMBER: HCC4S15D010BZ-HM40525930-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	909.3
2.5°	905.8
5°	910.1
7.5°	910.1
10°	905.8
12.5°	901.6
15°	897.3
17.5°	884.7
20°	858.4
22.5°	826.3
25°	789.9
27.5°	744.2
30°	685.7
32.5°	611.3
35°	523.1
37.5°	429.2
40°	339.5
42.5°	264.9
45°	205.7
47.5°	160.9
50°	125.3
52.5°	98.2
55°	79.6
57.5°	66.9
60°	59.2
62.5°	57.5
65°	57.5
67.5°	55.8
70°	49.9
72.5°	43.2
75°	36.4
77.5°	28.8
80°	22.1
82.5°	16.0
85°	10.1
87.5°	4.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)