

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579942

Luminaire Tested: **HCC4S15D010SL-HM40525935-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579942
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010SL-HM40525935-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1376.6 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579942
CATALOG NUMBER: HCC4S15D010SL-HM40525935-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P579942
 CATALOG NUMBER: HCC4S15D010SL-HM40525935-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82	78	76	74
5	91	83	77	72	90	82	76	72	80	75	72		78	74	71		77	73	70	69
6	87	78	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	66	62	81	72	66	62	71	65	62		69	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	57		65	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	70	61	55	51	69	60	54	51	59	54	50		58	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159449
5°	162373
10°	167382
15°	165533
20°	151988
25°	131129
30°	106863
35°	79113
40°	45390
45°	21944
50°	10458
55°	3634
60°	1307
65°	788
70°	649
75°	429
80°	0
85°	0



TEST NUMBER: P579942
 CATALOG NUMBER: HCC4S15D010SL-HM40525935-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	9.2
10°-20°	359.4	26.1
20°-30°	438.8	31.9
30°-40°	322.6	23.4
40°-50°	107.0	7.8
50°-60°	18.9	1.4
60°-70°	2.8	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.3	67.1
0°-40°	1246.9	90.6
0°-60°	1372.8	99.7
0°-90°	1376.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1376.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1293	
5°	1311	126
15°	1296	359
25°	964	439
35°	525	323
45°	126	107
55°	17	19
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579942
CATALOG NUMBER: HCC4S15D010SL-HM40525935-41MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1292.7
2.5°	1293.6
5°	1311.4
7.5°	1331.1
10°	1336.4
12.5°	1323.9
15°	1296.3
17.5°	1239.1
20°	1157.9
22.5°	1063.4
25°	963.5
27.5°	859.1
30°	750.3
32.5°	641.4
35°	525.4
37.5°	407.7
40°	281.9
42.5°	186.5
45°	125.8
47.5°	83.9
50°	54.5
52.5°	32.1
55°	16.9
57.5°	7.2
60°	5.3
62.5°	3.5
65°	2.7
67.5°	1.8
70°	1.8
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)