

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579947

Luminaire Tested: **HCC4W15D010MB-HM40525935-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010MB-HM40525935-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1260.8 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579947
CATALOG NUMBER: HCC4W15D010MB-HM40525935-41PSMDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579947

CATALOG NUMBER: HCC4W15D010MB-HM40525935-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109506
5°	108810
10°	106511
15°	104150
20°	99326
25°	91947
30°	79987
35°	60397
40°	43780
45°	34207
50°	29244
55°	25311
60°	23312
65°	21335
70°	19943
75°	18253
80°	17119
85°	16417



TEST NUMBER: P579947
 CATALOG NUMBER: HCC4W15D010MB-HM40525935-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	6.6
10°-20°	228.5	18.1
20°-30°	307.2	24.4
30°-40°	252.6	20.0
40°-50°	155.1	12.3
50°-60°	107.4	8.5
60°-70°	73.2	5.8
70°-80°	40.8	3.2
80°-90°	13.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.7	49.1
0°-40°	871.3	69.1
0°-60°	1133.8	89.9
0°-90°	1260.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1260.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	879	83
15°	816	228
25°	676	307
35°	401	253
45°	196	155
55°	118	107
65°	73	73
75°	38	41
85°	12	13
90°	0	



TEST NUMBER: P579947
CATALOG NUMBER: HCC4W15D010MB-HM40525935-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	887.8
2.5°	881.5
5°	878.8
7.5°	869.0
10°	850.4
12.5°	833.4
15°	815.6
17.5°	789.8
20°	756.7
22.5°	717.6
25°	675.6
27.5°	624.8
30°	561.6
32.5°	484.0
35°	401.1
37.5°	329.7
40°	271.9
42.5°	227.3
45°	196.1
47.5°	172.0
50°	152.4
52.5°	134.6
55°	117.7
57.5°	105.2
60°	94.5
62.5°	83.8
65°	73.1
67.5°	64.1
70°	55.3
72.5°	46.4
75°	38.3
77.5°	30.4
80°	24.1
82.5°	17.9
85°	11.6
87.5°	6.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)