

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592645

Luminaire Tested: **HCC4S15D010SL-HM40525950-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010SL-HM40525950-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1367.2 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592645
CATALOG NUMBER: HCC4S15D010SL-HM40525950-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P592645
 CATALOG NUMBER: HCC4S15D010SL-HM40525950-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63	62
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67	62	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201374
5°	201116
10°	197204
15°	183360
20°	157698
25°	126693
30°	98916
35°	69250
40°	35536
45°	18054
50°	9038
55°	3376
60°	1381
65°	1051
70°	649
75°	429
80°	639
85°	0



TEST NUMBER: P592645
 CATALOG NUMBER: HCC4S15D010SL-HM40525950-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	11.2
10°-20°	396.4	29.0
20°-30°	427.0	31.2
30°-40°	280.6	20.5
40°-50°	87.3	6.4
50°-60°	17.2	1.3
60°-70°	3.6	0.3
70°-80°	1.3	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.0	71.5
0°-40°	1257.5	92.0
0°-60°	1361.9	99.6
0°-90°	1367.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1367.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1633	
5°	1624	154
15°	1436	396
25°	931	427
35°	460	281
45°	104	87
55°	16	17
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P592645
CATALOG NUMBER: HCC4S15D010SL-HM40525950-41NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1632.6
2.5°	1624.3
5°	1624.3
7.5°	1611.4
10°	1574.5
12.5°	1515.4
15°	1435.9
17.5°	1329.7
20°	1201.4
22.5°	1062.9
25°	930.9
27.5°	808.1
30°	694.5
32.5°	587.3
35°	459.9
37.5°	320.4
40°	220.7
42.5°	152.4
45°	103.5
47.5°	70.2
50°	47.1
52.5°	29.6
55°	15.7
57.5°	6.5
60°	5.6
62.5°	4.7
65°	3.6
67.5°	2.7
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)