

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592639

Luminaire Tested: **HCC4S15D010MW-HM40525950-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010MW-HM40525950-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1491.1 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592639
CATALOG NUMBER: HCC4S15D010MW-HM40525950-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P592639
 CATALOG NUMBER: HCC4S15D010MW-HM40525950-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90	
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80	
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72	
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65	
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			59	
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			54	
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			49	
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			46	
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42	
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122408
5°	122987
10°	123833
15°	125066
20°	122992
25°	117329
30°	106607
35°	85980
40°	59657
45°	39179
50°	26251
55°	18688
60°	15961
65°	18358
70°	19655
75°	18920
80°	17048
85°	15709



TEST NUMBER: P592639
 CATALOG NUMBER: HCC4S15D010MW-HM40525950-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	6.3
10°-20°	275.1	18.5
20°-30°	393.1	26.4
30°-40°	351.2	23.6
40°-50°	180.2	12.1
50°-60°	81.9	5.5
60°-70°	61.1	4.1
70°-80°	41.5	2.8
80°-90°	12.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.9	51.2
0°-40°	1114.1	74.7
0°-60°	1376.2	92.3
0°-90°	1491.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1491.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	992	
5°	993	95
15°	979	275
25°	862	393
35°	571	351
45°	225	180
55°	87	82
65°	63	61
75°	40	42
85°	11	12
90°	0	



TEST NUMBER: P592639
CATALOG NUMBER: HCC4S15D010MW-HM40525950-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	992.4
2.5°	988.7
5°	993.3
7.5°	993.3
10°	988.7
12.5°	984.1
15°	979.4
17.5°	965.5
20°	937.0
22.5°	901.9
25°	862.1
27.5°	812.2
30°	748.5
32.5°	667.2
35°	571.0
37.5°	468.4
40°	370.5
42.5°	289.3
45°	224.6
47.5°	175.6
50°	136.8
52.5°	107.2
55°	86.9
57.5°	73.0
60°	64.7
62.5°	62.9
65°	62.9
67.5°	60.9
70°	54.5
72.5°	47.1
75°	39.7
77.5°	31.4
80°	24.0
82.5°	17.5
85°	11.1
87.5°	4.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)