

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579972

Luminaire Tested: **HCC4W20D010MW-HM40525827-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525827-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1568.7 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579972
CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579972
 CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93	
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85	
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78	
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72	
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66	
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61	
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56	
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52	
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49	
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156427
5°	156591
10°	156874
15°	159161
20°	155204
25°	145610
30°	128797
35°	97950
40°	61701
45°	35428
50°	18805
55°	7785
60°	2097
65°	1780
70°	1334
75°	1144
80°	923
85°	1840



TEST NUMBER: P579972
 CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	7.7
10°-20°	349.0	22.2
20°-30°	487.1	31.1
30°-40°	400.8	25.6
40°-50°	165.1	10.5
50°-60°	37.2	2.4
60°-70°	6.0	0.4
70°-80°	2.3	0.1
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.4	61.0
0°-40°	1357.2	86.5
0°-60°	1559.5	99.4
0°-90°	1568.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1568.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1268	
5°	1265	120
15°	1246	349
25°	1070	487
35°	650	401
45°	203	165
55°	36	37
65°	6	6
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P579972

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1268.2
2.5°	1262.2
5°	1264.7
7.5°	1259.8
10°	1252.5
12.5°	1248.9
15°	1246.4
17.5°	1224.8
20°	1182.4
22.5°	1129.2
25°	1069.9
27.5°	998.7
30°	904.3
32.5°	788.2
35°	650.5
37.5°	511.4
40°	383.2
42.5°	279.3
45°	203.1
47.5°	145.1
50°	98.0
52.5°	61.7
55°	36.2
57.5°	18.1
60°	8.5
62.5°	7.2
65°	6.1
67.5°	4.8
70°	3.7
72.5°	2.4
75°	2.4
77.5°	1.3
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)