

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579983

Luminaire Tested: **HCC4W20D010MW-HM40525827-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525827-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1710.1 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579983
CATALOG NUMBER: HCC4W20D010MW-HM40525827-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P579983

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148533
5°	147614
10°	144462
15°	141271
20°	134753
25°	124733
30°	108487
35°	81929
40°	59383
45°	46400
50°	39683
55°	34300
60°	31601
65°	28923
70°	27048
75°	24782
80°	23227
85°	22219



TEST NUMBER: P579983

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.6	6.6
10°-20°	309.9	18.1
20°-30°	416.7	24.4
30°-40°	342.6	20.0
40°-50°	210.4	12.3
50°-60°	145.6	8.5
60°-70°	99.3	5.8
70°-80°	55.3	3.2
80°-90°	17.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	839.2	49.1
0°-40°	1181.8	69.1
0°-60°	1537.9	89.9
0°-90°	1710.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1710.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1204	
5°	1192	113
15°	1106	310
25°	916	417
35°	544	343
45°	266	210
55°	160	146
65°	99	99
75°	52	55
85°	16	18
90°	0	



TEST NUMBER: P579983

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1204.2
2.5°	1195.7
5°	1192.2
7.5°	1178.9
10°	1153.4
12.5°	1130.5
15°	1106.3
17.5°	1071.3
20°	1026.6
22.5°	973.3
25°	916.5
27.5°	847.5
30°	761.7
32.5°	656.5
35°	544.1
37.5°	447.3
40°	368.8
42.5°	308.3
45°	266.0
47.5°	233.3
50°	206.8
52.5°	182.6
55°	159.5
57.5°	142.7
60°	128.1
62.5°	113.7
65°	99.1
67.5°	87.1
70°	75.0
72.5°	62.9
75°	52.0
77.5°	41.1
80°	32.7
82.5°	24.2
85°	15.7
87.5°	8.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)