

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P571728

Luminaire Tested: **HCC4S20D010SL-HM40525835-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P571728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010SL-HM40525835-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2009.6 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P571728
CATALOG NUMBER: HCC4S20D010SL-HM40525835-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P571728
 CATALOG NUMBER: HCC4S20D010SL-HM40525835-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295980
5°	295600
10°	289837
15°	269504
20°	231782
25°	186194
30°	145361
35°	101775
40°	52234
45°	26514
50°	13279
55°	4968
60°	1998
65°	1576
70°	1010
75°	667
80°	994
85°	0



TEST NUMBER: P571728
 CATALOG NUMBER: HCC4S20D010SL-HM40525835-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.7	11.2
10°-20°	582.6	29.0
20°-30°	627.6	31.2
30°-40°	412.3	20.5
40°-50°	128.2	6.4
50°-60°	25.2	1.3
60°-70°	5.3	0.3
70°-80°	2.0	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1435.9	71.5
0°-40°	1848.3	92.0
0°-60°	2001.6	99.6
0°-90°	2009.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2009.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2400	
5°	2387	226
15°	2110	583
25°	1368	628
35°	676	412
45°	152	128
55°	23	25
65°	5	5
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P571728
CATALOG NUMBER: HCC4S20D010SL-HM40525835-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2399.6
2.5°	2387.4
5°	2387.4
7.5°	2368.4
10°	2314.1
12.5°	2227.2
15°	2110.5
17.5°	1954.5
20°	1765.8
22.5°	1562.2
25°	1368.1
27.5°	1187.6
30°	1020.6
32.5°	863.2
35°	675.9
37.5°	471.0
40°	324.4
42.5°	223.9
45°	152.0
47.5°	103.1
50°	69.2
52.5°	43.5
55°	23.1
57.5°	9.5
60°	8.1
62.5°	6.8
65°	5.4
67.5°	4.0
70°	2.8
72.5°	2.8
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)