

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580040

Luminaire Tested: **HCC4S20D010MB-HM40525927-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010MB-HM40525927-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1670.0 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580040
CATALOG NUMBER: HCC4S20D010MB-HM40525927-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580040
 CATALOG NUMBER: HCC4S20D010MB-HM40525927-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72				
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65				
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59				
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54				
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49				
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137111
5°	137759
10°	138688
15°	140083
20°	137746
25°	131402
30°	119383
35°	96309
40°	66822
45°	43871
50°	29379
55°	20924
60°	17885
65°	20547
70°	21999
75°	21207
80°	19179
85°	17549



TEST NUMBER: P580040
 CATALOG NUMBER: HCC4S20D010MB-HM40525927-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.0	6.3
10°-20°	308.2	18.5
20°-30°	440.3	26.4
30°-40°	393.3	23.6
40°-50°	201.7	12.1
50°-60°	91.7	5.5
60°-70°	68.4	4.1
70°-80°	46.5	2.8
80°-90°	13.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.5	51.2
0°-40°	1247.8	74.7
0°-60°	1541.3	92.3
0°-90°	1670.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1670.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1112	
5°	1113	106
15°	1097	308
25°	966	440
35°	640	393
45°	252	202
55°	97	92
65°	70	68
75°	44	47
85°	12	14
90°	0	



TEST NUMBER: P580040
CATALOG NUMBER: HCC4S20D010MB-HM40525927-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1111.6
2.5°	1107.3
5°	1112.6
7.5°	1112.6
10°	1107.3
12.5°	1102.2
15°	1097.0
17.5°	1081.5
20°	1049.4
22.5°	1010.0
25°	965.5
27.5°	909.7
30°	838.2
32.5°	747.2
35°	639.6
37.5°	524.8
40°	415.0
42.5°	323.9
45°	251.5
47.5°	196.6
50°	153.1
52.5°	120.1
55°	97.3
57.5°	81.8
60°	72.5
62.5°	70.4
65°	70.4
67.5°	68.4
70°	61.0
72.5°	52.8
75°	44.5
77.5°	35.2
80°	27.0
82.5°	19.6
85°	12.4
87.5°	5.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)