

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580048

Luminaire Tested: **HCC4W20D010BZ-HM40525927-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010BZ-HM40525927-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1494.0 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580048
CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580048

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126664
5°	125996
10°	123695
15°	121082
20°	115917
25°	107775
30°	95384
35°	75289
40°	56340
45°	43330
50°	35174
55°	29160
60°	25804
65°	23874
70°	22035
75°	20207
80°	18397
85°	14577



TEST NUMBER: P580048
 CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	6.4
10°-20°	265.9	17.8
20°-30°	361.1	24.2
30°-40°	312.8	20.9
40°-50°	196.4	13.1
50°-60°	123.6	8.3
60°-70°	81.2	5.4
70°-80°	44.7	3.0
80°-90°	12.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.2	48.4
0°-40°	1036.0	69.3
0°-60°	1355.9	90.8
0°-90°	1494.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1494.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1027	
5°	1018	96
15°	948	266
25°	792	361
35°	500	313
45°	248	196
55°	136	124
65°	82	81
75°	42	45
85°	10	12
90°	0	



TEST NUMBER: P580048
CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1026.9
2.5°	1020.7
5°	1017.6
7.5°	1007.3
10°	987.6
12.5°	968.0
15°	948.2
17.5°	921.4
20°	883.1
22.5°	839.6
25°	791.9
27.5°	737.1
30°	669.7
32.5°	588.0
35°	500.0
37.5°	419.2
40°	349.9
42.5°	295.0
45°	248.4
47.5°	213.2
50°	183.3
52.5°	157.4
55°	135.6
57.5°	117.0
60°	104.6
62.5°	93.1
65°	81.8
67.5°	70.4
70°	61.1
72.5°	50.7
75°	42.4
77.5°	33.1
80°	25.9
82.5°	17.5
85°	10.3
87.5°	4.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)