

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580095

Luminaire Tested: **HCC4S20D010MW-HM40525940-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010MW-HM40525940-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1847.0 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580095
CATALOG NUMBER: HCC4S20D010MW-HM40525940-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P580095
 CATALOG NUMBER: HCC4S20D010MW-HM40525940-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239105
5°	234113
10°	221239
15°	206639
20°	188991
25°	168760
30°	141715
35°	99682
40°	61508
45°	36806
50°	21703
55°	10795
60°	5575
65°	3677
70°	2272
75°	1811
80°	923
85°	1840



TEST NUMBER: P580095
 CATALOG NUMBER: HCC4S20D010MW-HM40525940-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.6	9.6
10°-20°	452.3	24.5
20°-30°	564.1	30.5
30°-40°	415.5	22.5
40°-50°	170.9	9.3
50°-60°	49.9	2.7
60°-70°	12.8	0.7
70°-80°	4.0	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1193.0	64.6
0°-40°	1608.5	87.1
0°-60°	1829.3	99.0
0°-90°	1847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1847.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1938	
5°	1891	177
15°	1618	452
25°	1240	564
35°	662	416
45°	211	171
55°	50	50
65°	13	13
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P580095
CATALOG NUMBER: HCC4S20D010MW-HM40525940-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1938.5
2.5°	1918.5
5°	1890.8
7.5°	1840.6
10°	1766.4
12.5°	1693.5
15°	1618.2
17.5°	1534.0
20°	1439.8
22.5°	1341.8
25°	1240.0
27.5°	1126.9
30°	995.0
32.5°	835.5
35°	662.0
37.5°	508.8
40°	382.0
42.5°	282.6
45°	211.0
47.5°	155.8
50°	113.1
52.5°	77.9
55°	50.2
57.5°	30.2
60°	22.6
62.5°	16.3
65°	12.6
67.5°	8.8
70°	6.3
72.5°	5.0
75°	3.8
77.5°	2.5
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)