

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592686

Luminaire Tested: **HCC4W20D010SL-HM40525950-41WDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W20D010SL-HM40525950-41WDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1872.2 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592686  
CATALOG NUMBER: HCC4W20D010SL-HM40525950-41WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P592686

CATALOG NUMBER: HCC4W20D010SL-HM40525950-41WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	149668	149668	149668
5°	149298	149459	149459
10°	147568	147731	147568
15°	145804	145804	145804
20°	139820	140148	140306
25°	130789	130952	131293
30°	117175	117545	117545
35°	95135	95888	96083
40°	71813	72216	72409
45°	55000	54773	54773
50°	45325	45075	45075
55°	38902	38622	38622
60°	34709	34413	34413
65°	32630	32630	32630
70°	30366	30366	30366
75°	27546	28165	27546
80°	25927	25003	25927
85°	21228	21228	21228



TEST NUMBER: P592686  
 CATALOG NUMBER: HCC4W20D010SL-HM40525950-41WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.3	6.1
10°-20°	319.9	17.1
20°-30°	439.6	23.5
30°-40°	395.3	21.1
40°-50°	249.8	13.3
50°-60°	163.1	8.7
60°-70°	110.5	5.9
70°-80°	62.2	3.3
80°-90°	17.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.9	46.7
0°-40°	1269.2	67.8
0°-60°	1682.0	89.8
0°-90°	1872.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1872.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1213	1213	1213	1213	1213	
5°	1206	1206	1207	1207	1207	114
15°	1142	1142	1142	1142	1142	320
25°	961	962	962	965	965	439
35°	632	634	637	639	638	393
45°	315	314	314	314	314	250
55°	181	181	180	181	180	164
65°	112	112	112	112	112	111
75°	58	59	59	59	58	62
85°	15	15	15	15	15	18
90°	0	0	0	0	0	



TEST NUMBER: P592686

CATALOG NUMBER: HCC4W20D010SL-HM40525950-41WDW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1213.4	1213.4	1213.4	1213.4	1213.4
2.5°	1207.1	1207.1	1207.1	1207.1	1207.1
5°	1205.8	1205.8	1207.1	1207.1	1207.1
7.5°	1197.0	1198.3	1198.3	1198.3	1198.3
10°	1178.2	1178.2	1179.5	1179.5	1178.2
12.5°	1160.6	1160.6	1160.6	1161.9	1160.6
15°	1141.8	1141.8	1141.8	1141.8	1141.8
17.5°	1109.1	1110.4	1110.4	1110.4	1110.4
20°	1065.2	1067.7	1067.7	1068.9	1068.9
22.5°	1015.0	1016.2	1017.4	1018.7	1017.4
25°	961.0	962.2	962.2	964.7	964.7
27.5°	898.1	899.4	901.9	901.9	901.9
30°	822.7	824.0	825.3	825.3	825.3
32.5°	733.6	733.6	736.0	737.3	736.0
35°	631.8	634.3	636.8	639.3	638.1
37.5°	535.1	537.6	538.9	538.9	540.1
40°	446.0	448.5	448.5	450.9	449.7
42.5°	375.5	374.3	374.3	376.8	375.5
45°	315.3	314.0	314.0	314.0	314.0
47.5°	271.3	270.1	270.1	270.1	270.1
50°	236.2	234.9	234.9	234.9	234.9
52.5°	207.3	206.0	206.0	206.0	204.7
55°	180.9	180.9	179.6	180.9	179.6
57.5°	157.0	157.0	157.0	157.0	157.0
60°	140.7	139.5	139.5	139.5	139.5
62.5°	125.6	125.6	125.6	125.6	125.6
65°	111.8	111.8	111.8	111.8	111.8
67.5°	98.0	96.7	98.0	98.0	96.7
70°	84.2	82.9	84.2	84.2	84.2
72.5°	70.3	70.3	70.3	71.6	70.3
75°	57.8	59.1	59.1	59.1	57.8
77.5°	46.5	47.7	46.5	46.5	46.5
80°	36.5	35.2	35.2	35.2	36.5
82.5°	25.1	25.1	25.1	25.1	25.1
85°	15.0	15.0	15.0	15.0	15.0
87.5°	6.3	6.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)