

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580114

Luminaire Tested: **HCC4W25D010SL-HM40525827-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010SL-HM40525827-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2049.1 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580114
CATALOG NUMBER: HCC4W25D010SL-HM40525827-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580114
 CATALOG NUMBER: HCC4W25D010SL-HM40525827-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63			63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54			54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51			51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265773
5°	260944
10°	247516
15°	231438
20°	210189
25°	186004
30°	154704
35°	111548
40°	69623
45°	40155
50°	22662
55°	10774
60°	6192
65°	4757
70°	3174
75°	2097
80°	2060
85°	2123



TEST NUMBER: P580114
 CATALOG NUMBER: HCC4W25D010SL-HM40525827-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.0	9.6
10°-20°	505.6	24.7
20°-30°	621.8	30.3
30°-40°	461.8	22.5
40°-50°	187.7	9.2
50°-60°	52.0	2.5
60°-70°	16.2	0.8
70°-80°	5.4	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1324.4	64.6
0°-40°	1786.2	87.2
0°-60°	2025.9	98.9
0°-90°	2049.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2049.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2155	
5°	2108	197
15°	1812	506
25°	1367	622
35°	741	462
45°	230	188
55°	50	52
65°	16	16
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P580114
CATALOG NUMBER: HCC4W25D010SL-HM40525827-41NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2154.7
2.5°	2134.0
5°	2107.5
7.5°	2054.3
10°	1976.2
12.5°	1895.0
15°	1812.4
17.5°	1713.5
20°	1601.3
22.5°	1487.7
25°	1366.7
27.5°	1235.2
30°	1086.2
32.5°	916.5
35°	740.8
37.5°	575.6
40°	432.4
42.5°	315.8
45°	230.2
47.5°	165.3
50°	118.1
52.5°	81.2
55°	50.1
57.5°	32.5
60°	25.1
62.5°	20.7
65°	16.3
67.5°	11.9
70°	8.8
72.5°	7.3
75°	4.4
77.5°	2.9
80°	2.9
82.5°	1.5
85°	1.5
87.5°	1.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)