

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580122

Luminaire Tested: **HCC4W25D010MB-HM40525827-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525827-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2087.6 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580122
CATALOG NUMBER: HCC4W25D010MB-HM40525827-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580122

CATALOG NUMBER: HCC4W25D010MB-HM40525827-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181330
5°	180191
10°	176362
15°	172455
20°	164484
25°	152252
30°	132429
35°	100013
40°	72473
45°	56640
50°	48414
55°	41913
60°	38607
65°	35315
70°	33034
75°	30215
80°	28342
85°	27172



TEST NUMBER: P580122
 CATALOG NUMBER: HCC4W25D010MB-HM40525827-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.4	6.6
10°-20°	378.3	18.1
20°-30°	508.7	24.4
30°-40°	418.3	20.0
40°-50°	256.8	12.3
50°-60°	177.8	8.5
60°-70°	121.2	5.8
70°-80°	67.5	3.2
80°-90°	21.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1024.4	49.1
0°-40°	1442.7	69.1
0°-60°	1877.3	89.9
0°-90°	2087.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2087.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1470	
5°	1455	137
15°	1350	378
25°	1119	509
35°	664	418
45°	325	257
55°	195	178
65°	121	121
75°	63	68
85°	19	22
90°	0	



TEST NUMBER: P580122
CATALOG NUMBER: HCC4W25D010MB-HM40525827-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1470.1
2.5°	1459.7
5°	1455.3
7.5°	1439.0
10°	1408.1
12.5°	1380.0
15°	1350.5
17.5°	1307.7
20°	1253.1
22.5°	1188.2
25°	1118.7
27.5°	1034.6
30°	929.8
32.5°	801.5
35°	664.2
37.5°	546.1
40°	450.1
42.5°	376.4
45°	324.7
47.5°	284.8
50°	252.3
52.5°	222.9
55°	194.9
57.5°	174.2
60°	156.5
62.5°	138.8
65°	121.0
67.5°	106.2
70°	91.6
72.5°	76.8
75°	63.4
77.5°	50.1
80°	39.9
82.5°	29.5
85°	19.2
87.5°	10.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)