

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580141

Luminaire Tested: **HCC4W25D010BZ-HM40525830-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010BZ-HM40525830-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2382.6 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580141
CATALOG NUMBER: HCC4W25D010BZ-HM40525830-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580141

CATALOG NUMBER: HCC4W25D010BZ-HM40525830-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39			39
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	190470	190470	190470
5°	190009	190207	190207
10°	187797	187998	187797
15°	185556	185556	185556
20°	177938	178358	178555
25°	166433	166651	167086
30°	149121	149591	149591
35°	121079	122043	122284
40°	91361	91892	92150
45°	69984	69722	69722
50°	57663	57376	57376
55°	49504	49160	49160
60°	44182	43788	43788
65°	41532	41532	41532
70°	38624	38624	38624
75°	35028	35790	35028
80°	32959	31751	32959
85°	27172	27172	27172



TEST NUMBER: P580141

CATALOG NUMBER: HCC4W25D010BZ-HM40525830-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.5	6.1
10°-20°	407.2	17.1
20°-30°	559.5	23.5
30°-40°	503.1	21.1
40°-50°	317.9	13.3
50°-60°	207.5	8.7
60°-70°	140.6	5.9
70°-80°	79.1	3.3
80°-90°	22.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.1	46.7
0°-40°	1615.2	67.8
0°-60°	2140.6	89.8
0°-90°	2382.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2382.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1544	1544	1544	1544	1544	
5°	1535	1535	1536	1536	1536	145
15°	1453	1453	1453	1453	1453	407
25°	1223	1224	1224	1228	1228	558
35°	804	807	810	814	812	501
45°	401	400	400	400	400	318
55°	230	230	229	230	229	208
65°	142	142	142	142	142	141
75°	74	75	75	75	74	79
85°	19	19	19	19	19	22
90°	0	0	0	0	0	



TEST NUMBER: P580141

CATALOG NUMBER: HCC4W25D010BZ-HM40525830-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1544.2	1544.2	1544.2	1544.2	1544.2
2.5°	1536.2	1536.2	1536.2	1536.2	1536.2
5°	1534.6	1534.6	1536.2	1536.2	1536.2
7.5°	1523.5	1525.1	1525.1	1525.1	1525.1
10°	1499.4	1499.4	1501.0	1501.0	1499.4
12.5°	1477.1	1477.1	1477.1	1478.7	1477.1
15°	1453.1	1453.1	1453.1	1453.1	1453.1
17.5°	1411.5	1413.2	1413.2	1413.2	1413.2
20°	1355.6	1358.8	1358.8	1360.3	1360.3
22.5°	1291.7	1293.3	1294.9	1296.4	1294.9
25°	1222.9	1224.5	1224.5	1227.7	1227.7
27.5°	1143.0	1144.6	1147.7	1147.7	1147.7
30°	1047.0	1048.6	1050.3	1050.3	1050.3
32.5°	933.6	933.6	936.7	938.3	936.7
35°	804.1	807.2	810.5	813.7	812.1
37.5°	681.0	684.2	685.8	685.8	687.3
40°	567.4	570.7	570.7	573.9	572.3
42.5°	478.0	476.3	476.3	479.6	478.0
45°	401.2	399.7	399.7	399.7	399.7
47.5°	345.2	343.7	343.7	343.7	343.7
50°	300.5	299.0	299.0	299.0	299.0
52.5°	263.7	262.2	262.2	262.2	260.6
55°	230.2	230.2	228.6	230.2	228.6
57.5°	199.8	199.8	199.8	199.8	199.8
60°	179.1	177.5	177.5	177.5	177.5
62.5°	159.9	159.9	159.9	159.9	159.9
65°	142.3	142.3	142.3	142.3	142.3
67.5°	124.6	123.1	124.6	124.6	123.1
70°	107.1	105.6	107.1	107.1	107.1
72.5°	89.5	89.5	89.5	91.1	89.5
75°	73.5	75.1	75.1	75.1	73.5
77.5°	59.2	60.7	59.2	59.2	59.2
80°	46.4	44.7	44.7	44.7	46.4
82.5°	32.0	32.0	32.0	32.0	32.0
85°	19.2	19.2	19.2	19.2	19.2
87.5°	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)