

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580138

Luminaire Tested: **HCC4W25D010MB-HM40525830-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525830-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2308.9 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580138
CATALOG NUMBER: HCC4W25D010MB-HM40525830-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580138
 CATALOG NUMBER: HCC4W25D010MB-HM40525830-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	97		97	95	94		94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84		89	85	82		86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60		69	64	59		67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62	57	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39		48	43	39		48	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195750
5°	194727
10°	191167
15°	187127
20°	179120
25°	166555
30°	147426
35°	116351
40°	87078
45°	66984
50°	54344
55°	45052
60°	39865
65°	36862
70°	34044
75°	31263
80°	28413
85°	22644



TEST NUMBER: P580138
 CATALOG NUMBER: HCC4W25D010MB-HM40525830-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	6.4
10°-20°	411.0	17.8
20°-30°	558.0	24.2
30°-40°	483.4	20.9
40°-50°	303.5	13.1
50°-60°	190.9	8.3
60°-70°	125.4	5.4
70°-80°	69.2	3.0
80°-90°	18.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1117.6	48.4
0°-40°	1601.0	69.3
0°-60°	2095.4	90.8
0°-90°	2308.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2308.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1587	
5°	1573	149
15°	1465	411
25°	1224	558
35°	773	483
45°	384	304
55°	210	191
65°	126	125
75°	66	69
85°	16	19
90°	0	



TEST NUMBER: P580138
CATALOG NUMBER: HCC4W25D010MB-HM40525830-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1587.0
2.5°	1577.4
5°	1572.7
7.5°	1556.7
10°	1526.3
12.5°	1495.8
15°	1465.4
17.5°	1423.9
20°	1364.6
22.5°	1297.4
25°	1223.8
27.5°	1139.0
30°	1035.1
32.5°	908.7
35°	772.7
37.5°	647.9
40°	540.8
42.5°	456.0
45°	384.0
47.5°	329.6
50°	283.2
52.5°	243.2
55°	209.5
57.5°	180.8
60°	161.6
62.5°	143.9
65°	126.3
67.5°	108.8
70°	94.4
72.5°	78.4
75°	65.6
77.5°	51.1
80°	40.0
82.5°	27.2
85°	16.0
87.5°	6.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)