

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580157

Luminaire Tested: **HCC4W25D010MW-HM40525835-41NDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W25D010MW-HM40525835-41NDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2280.6 lumens  
Efficiency: N/A  
Efficacy: 85.1 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580157  
CATALOG NUMBER: HCC4W25D010MW-HM40525835-41NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580157  
 CATALOG NUMBER: HCC4W25D010MW-HM40525835-41NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	200363
5°	198875
10°	193697
15°	188608
20°	180157
25°	167835
30°	147797
35°	116547
40°	84598
45°	62169
50°	50563
55°	42407
60°	38434
65°	35315
70°	32890
75°	30024
80°	27134
85°	23493



TEST NUMBER: P580157  
 CATALOG NUMBER: HCC4W25D010MW-HM40525835-41NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.4	6.6
10°-20°	414.3	18.2
20°-30°	561.5	24.6
30°-40°	481.9	21.1
40°-50°	284.5	12.5
50°-60°	180.3	7.9
60°-70°	121.1	5.3
70°-80°	66.9	2.9
80°-90°	18.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1127.2	49.4
0°-40°	1609.1	70.6
0°-60°	2073.9	90.9
0°-90°	2280.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2280.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1624	
5°	1606	151
15°	1477	414
25°	1233	562
35°	774	482
45°	356	285
55°	197	180
65°	121	121
75°	63	67
85°	17	19
90°	0	



TEST NUMBER: P580157  
CATALOG NUMBER: HCC4W25D010MW-HM40525835-41NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1624.4
2.5°	1612.9
5°	1606.2
7.5°	1584.7
10°	1546.5
12.5°	1513.4
15°	1477.0
17.5°	1430.4
20°	1372.5
22.5°	1307.8
25°	1233.2
27.5°	1145.4
30°	1037.7
32.5°	910.0
35°	774.0
37.5°	643.2
40°	525.4
42.5°	427.7
45°	356.4
47.5°	304.9
50°	263.5
52.5°	228.7
55°	197.2
57.5°	172.4
60°	155.8
62.5°	139.2
65°	121.0
67.5°	106.1
70°	91.2
72.5°	76.2
75°	63.0
77.5°	49.7
80°	38.2
82.5°	26.5
85°	16.6
87.5°	6.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)