

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580159

Luminaire Tested: **HCC4W25D010SL-HM40525835-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010SL-HM40525835-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2469.6 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580159
CATALOG NUMBER: HCC4W25D010SL-HM40525835-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P580159

CATALOG NUMBER: HCC4W25D010SL-HM40525835-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	197427	197427	197427
5°	196943	197153	197153
10°	194674	194874	194674
15°	192337	192337	192337
20°	184449	184869	185092
25°	172516	172734	173197
30°	154576	155046	155046
35°	125491	126500	126756
40°	94710	95257	95515
45°	72548	72252	72252
50°	59774	59467	59467
55°	51310	50966	50966
60°	45786	45367	45367
65°	43020	43020	43020
70°	40031	40031	40031
75°	36315	37125	36315
80°	34166	32959	34166
85°	28163	28163	28163



TEST NUMBER: P580159
 CATALOG NUMBER: HCC4W25D010SL-HM40525835-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	6.1
10°-20°	422.0	17.1
20°-30°	579.9	23.5
30°-40°	521.4	21.1
40°-50°	329.5	13.3
50°-60°	215.1	8.7
60°-70°	145.7	5.9
70°-80°	82.0	3.3
80°-90°	23.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1152.8	46.7
0°-40°	1674.2	67.8
0°-60°	2218.8	89.8
0°-90°	2469.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2469.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1601	1601	1601	1601	1601	
5°	1591	1591	1592	1592	1592	151
15°	1506	1506	1506	1506	1506	422
25°	1268	1269	1269	1273	1273	579
35°	833	837	840	843	842	519
45°	416	414	414	414	414	330
55°	239	239	237	239	237	216
65°	147	147	147	147	147	146
75°	76	78	78	78	76	82
85°	20	20	20	20	20	23
90°	0	0	0	0	0	



TEST NUMBER: P580159

CATALOG NUMBER: HCC4W25D010SL-HM40525835-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1600.6	1600.6	1600.6	1600.6	1600.6
2.5°	1592.3	1592.3	1592.3	1592.3	1592.3
5°	1590.6	1590.6	1592.3	1592.3	1592.3
7.5°	1579.1	1580.7	1580.7	1580.7	1580.7
10°	1554.3	1554.3	1555.9	1555.9	1554.3
12.5°	1531.0	1531.0	1531.0	1532.7	1531.0
15°	1506.2	1506.2	1506.2	1506.2	1506.2
17.5°	1463.1	1464.8	1464.8	1464.8	1464.8
20°	1405.2	1408.4	1408.4	1410.1	1410.1
22.5°	1338.9	1340.5	1342.2	1343.8	1342.2
25°	1267.6	1269.2	1269.2	1272.6	1272.6
27.5°	1184.8	1186.4	1189.7	1189.7	1189.7
30°	1085.3	1087.0	1088.6	1088.6	1088.6
32.5°	967.7	967.7	970.9	972.6	970.9
35°	833.4	836.8	840.1	843.4	841.8
37.5°	705.9	709.2	710.8	710.8	712.5
40°	588.2	591.6	591.6	594.9	593.2
42.5°	495.4	493.8	493.8	497.1	495.4
45°	415.9	414.2	414.2	414.2	414.2
47.5°	357.9	356.2	356.2	356.2	356.2
50°	311.5	309.9	309.9	309.9	309.9
52.5°	273.4	271.8	271.8	271.8	270.1
55°	238.6	238.6	237.0	238.6	237.0
57.5°	207.2	207.2	207.2	207.2	207.2
60°	185.6	183.9	183.9	183.9	183.9
62.5°	165.7	165.7	165.7	165.7	165.7
65°	147.4	147.4	147.4	147.4	147.4
67.5°	129.3	127.6	129.3	129.3	127.6
70°	111.0	109.4	111.0	111.0	111.0
72.5°	92.8	92.8	92.8	94.5	92.8
75°	76.2	77.9	77.9	77.9	76.2
77.5°	61.3	63.0	61.3	61.3	61.3
80°	48.1	46.4	46.4	46.4	48.1
82.5°	33.2	33.2	33.2	33.2	33.2
85°	19.9	19.9	19.9	19.9	19.9
87.5°	8.2	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)