

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592699

Luminaire Tested: **HCC4S25D010MB-HM40525850-41NDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592699  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S25D010MB-HM40525850-41NDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2520.8 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592699  
CATALOG NUMBER: HCC4S25D010MB-HM40525850-41NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P592699  
 CATALOG NUMBER: HCC4S25D010MB-HM40525850-41NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63	62
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67	62	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	371283
5°	370807
10°	363584
15°	338077
20°	290745
25°	233569
30°	182350
35°	127674
40°	65518
45°	33265
50°	16656
55°	6215
60°	2516
65°	1985
70°	1226
75°	810
80°	1208
85°	0



TEST NUMBER: P592699  
 CATALOG NUMBER: HCC4S25D010MB-HM40525850-41NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	283.1	11.2
10°-20°	730.8	29.0
20°-30°	787.3	31.2
30°-40°	517.3	20.5
40°-50°	160.8	6.4
50°-60°	31.6	1.3
60°-70°	6.7	0.3
70°-80°	2.5	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1801.2	71.5
0°-40°	2318.5	92.0
0°-60°	2510.9	99.6
0°-90°	2520.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2520.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3010	
5°	2995	283
15°	2648	731
25°	1716	787
35°	848	517
45°	191	161
55°	29	32
65°	7	7
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P592699

CATALOG NUMBER: HCC4S25D010MB-HM40525850-41NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3010.1
2.5°	2994.8
5°	2994.8
7.5°	2971.0
10°	2902.9
12.5°	2793.9
15°	2647.5
17.5°	2451.6
20°	2215.0
22.5°	1959.6
25°	1716.2
27.5°	1489.7
30°	1280.3
32.5°	1082.8
35°	847.9
37.5°	590.8
40°	406.9
42.5°	280.9
45°	190.7
47.5°	129.4
50°	86.8
52.5°	54.5
55°	28.9
57.5°	12.0
60°	10.2
62.5°	8.5
65°	6.8
67.5°	5.1
70°	3.4
72.5°	3.4
75°	1.7
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)