

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580191

Luminaire Tested: **HCC4W25D010MW-HM40525927-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580191  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W25D010MW-HM40525927-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2143.3 lumens  
Efficiency: N/A  
Efficacy: 80.0 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580191  
CATALOG NUMBER: HCC4W25D010MW-HM40525927-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P580191  
 CATALOG NUMBER: HCC4W25D010MW-HM40525927-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	173153
5°	175684
10°	181197
15°	193614
20°	205162
25°	202920
30°	182122
35°	141753
40°	96014
45°	59954
50°	25963
55°	8688
60°	2171
65°	1488
70°	902
75°	572
80°	852
85°	0



TEST NUMBER: P580191  
 CATALOG NUMBER: HCC4W25D010MW-HM40525927-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.3	6.4
10°-20°	430.4	20.1
20°-30°	674.4	31.5
30°-40°	582.1	27.2
40°-50°	267.7	12.5
50°-60°	45.4	2.1
60°-70°	5.1	0.2
70°-80°	1.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.1	57.9
0°-40°	1823.1	85.1
0°-60°	2136.3	99.7
0°-90°	2143.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2143.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1404	
5°	1419	136
15°	1516	430
25°	1491	674
35°	941	582
45°	344	268
55°	40	45
65°	5	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P580191  
CATALOG NUMBER: HCC4W25D010MW-HM40525927-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1403.8
2.5°	1403.8
5°	1418.9
7.5°	1432.8
10°	1446.7
12.5°	1475.8
15°	1516.2
17.5°	1550.3
20°	1563.0
22.5°	1544.0
25°	1491.0
27.5°	1405.0
30°	1278.7
32.5°	1119.5
35°	941.4
37.5°	762.0
40°	596.3
42.5°	456.1
45°	343.7
47.5°	241.4
50°	135.3
52.5°	74.5
55°	40.4
57.5°	20.2
60°	8.8
62.5°	6.3
65°	5.1
67.5°	3.8
70°	2.5
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)