

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580192

Luminaire Tested: **HCC4S25D010MB-HM40525927-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010MB-HM40525927-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1823.8 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580192
CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580192

CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154626
5°	153805
10°	150987
15°	147822
20°	141500
25°	131578
30°	116449
35°	91897
40°	68770
45°	52889
50°	42926
55°	35590
60°	31502
65°	29128
70°	26868
75°	24686
80°	22446
85°	17832



TEST NUMBER: P580192
 CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	6.4
10°-20°	324.6	17.8
20°-30°	440.8	24.2
30°-40°	381.8	20.9
40°-50°	239.7	13.1
50°-60°	150.8	8.3
60°-70°	99.0	5.4
70°-80°	54.6	3.0
80°-90°	15.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.9	48.4
0°-40°	1264.7	69.3
0°-60°	1655.2	90.8
0°-90°	1823.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1823.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1254	
5°	1242	117
15°	1158	325
25°	967	441
35°	610	382
45°	303	240
55°	166	151
65°	100	99
75°	52	55
85°	13	15
90°	0	



TEST NUMBER: P580192
CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1253.6
2.5°	1246.0
5°	1242.2
7.5°	1229.6
10°	1205.5
12.5°	1181.6
15°	1157.6
17.5°	1124.7
20°	1078.0
22.5°	1024.9
25°	966.8
27.5°	899.7
30°	817.6
32.5°	717.8
35°	610.3
37.5°	511.8
40°	427.1
42.5°	360.2
45°	303.2
47.5°	260.3
50°	223.7
52.5°	192.0
55°	165.5
57.5°	142.8
60°	127.7
62.5°	113.7
65°	99.8
67.5°	85.9
70°	74.5
72.5°	61.9
75°	51.8
77.5°	40.4
80°	31.6
82.5°	21.5
85°	12.6
87.5°	5.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)