

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580194

Luminaire Tested: **HCC4W25D010BZ-HM40525927-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580194  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W25D010BZ-HM40525927-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1785.9 lumens  
Efficiency: N/A  
Efficacy: 66.6 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580194  
CATALOG NUMBER: HCC4W25D010BZ-HM40525927-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580194  
 CATALOG NUMBER: HCC4W25D010BZ-HM40525927-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	155132
5°	154164
10°	150874
15°	147541
20°	140726
25°	130272
30°	113301
35°	85558
40°	62007
45°	48459
50°	41449
55°	35827
60°	33032
65°	30208
70°	28202
75°	25878
80°	24222
85°	23210



TEST NUMBER: P580194  
 CATALOG NUMBER: HCC4W25D010BZ-HM40525927-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.6	6.6
10°-20°	323.6	18.1
20°-30°	435.2	24.4
30°-40°	357.8	20.0
40°-50°	219.8	12.3
50°-60°	152.1	8.5
60°-70°	103.7	5.8
70°-80°	57.8	3.2
80°-90°	18.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	876.4	49.1
0°-40°	1234.2	69.1
0°-60°	1606.1	89.9
0°-90°	1785.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1785.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1258	
5°	1245	118
15°	1155	324
25°	957	435
35°	568	358
45°	278	220
55°	167	152
65°	104	104
75°	54	58
85°	16	18
90°	0	



TEST NUMBER: P580194  
CATALOG NUMBER: HCC4W25D010BZ-HM40525927-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1257.7
2.5°	1248.8
5°	1245.1
7.5°	1231.2
10°	1204.6
12.5°	1180.6
15°	1155.4
17.5°	1118.7
20°	1072.1
22.5°	1016.4
25°	957.2
27.5°	885.1
30°	795.5
32.5°	685.6
35°	568.2
37.5°	467.2
40°	385.1
42.5°	322.0
45°	277.8
47.5°	243.8
50°	216.0
52.5°	190.7
55°	166.6
57.5°	149.0
60°	133.9
62.5°	118.7
65°	103.5
67.5°	90.9
70°	78.2
72.5°	65.7
75°	54.3
77.5°	42.9
80°	34.1
82.5°	25.3
85°	16.4
87.5°	8.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)