

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580228

Luminaire Tested: **HCC4S25D010MW-HM40525935-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010MW-HM40525935-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2137.4 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580228
CATALOG NUMBER: HCC4S25D010MW-HM40525935-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580228
 CATALOG NUMBER: HCC4S25D010MW-HM40525935-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181219
5°	180252
10°	176951
15°	173233
20°	165810
25°	154198
30°	136474
35°	107708
40°	80605
45°	61995
50°	50314
55°	41719
60°	36905
65°	34148
70°	31520
75°	28928
80°	26282
85°	20945



TEST NUMBER: P580228
 CATALOG NUMBER: HCC4S25D010MW-HM40525935-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	6.4
10°-20°	380.4	17.8
20°-30°	516.6	24.2
30°-40°	447.5	20.9
40°-50°	280.9	13.1
50°-60°	176.7	8.3
60°-70°	116.1	5.4
70°-80°	64.0	3.0
80°-90°	17.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.6	48.4
0°-40°	1482.1	69.3
0°-60°	1939.8	90.8
0°-90°	2137.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2137.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1469	
5°	1456	138
15°	1357	380
25°	1133	517
35°	715	447
45°	355	281
55°	194	177
65°	117	116
75°	61	64
85°	15	18
90°	0	



TEST NUMBER: P580228

CATALOG NUMBER: HCC4S25D010MW-HM40525935-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1469.2
2.5°	1460.2
5°	1455.8
7.5°	1440.9
10°	1412.8
12.5°	1384.7
15°	1356.6
17.5°	1318.1
20°	1263.2
22.5°	1201.0
25°	1133.0
27.5°	1054.5
30°	958.2
32.5°	841.2
35°	715.3
37.5°	599.8
40°	500.6
42.5°	422.1
45°	355.4
47.5°	305.1
50°	262.2
52.5°	225.1
55°	194.0
57.5°	167.3
60°	149.6
62.5°	133.3
65°	117.0
67.5°	100.7
70°	87.4
72.5°	72.6
75°	60.7
77.5°	47.4
80°	37.0
82.5°	25.2
85°	14.8
87.5°	5.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)