

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580220

Luminaire Tested: **HCC4W25D010BZ-HM40525935-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010BZ-HM40525935-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2389.1 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580220
CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580220
 CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196132
5°	197067
10°	198419
15°	200407
20°	197050
25°	187991
30°	170799
35°	137763
40°	95595
45°	62762
50°	42043
55°	29934
60°	25557
65°	29390
70°	31520
75°	30358
80°	27347
85°	25050



TEST NUMBER: P580220
 CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.7	6.3
10°-20°	440.9	18.5
20°-30°	629.9	26.4
30°-40°	562.7	23.6
40°-50°	288.6	12.1
50°-60°	131.2	5.5
60°-70°	97.9	4.1
70°-80°	66.6	2.8
80°-90°	19.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1222.4	51.2
0°-40°	1785.1	74.7
0°-60°	2204.9	92.3
0°-90°	2389.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2389.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1590	
5°	1592	152
15°	1569	441
25°	1381	630
35°	915	563
45°	360	289
55°	139	131
65°	101	98
75°	64	67
85°	18	20
90°	0	



TEST NUMBER: P580220
CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1590.1
2.5°	1584.2
5°	1591.6
7.5°	1591.6
10°	1584.2
12.5°	1576.8
15°	1569.4
17.5°	1547.2
20°	1501.2
22.5°	1445.0
25°	1381.3
27.5°	1301.4
30°	1199.2
32.5°	1068.9
35°	914.9
37.5°	750.7
40°	593.7
42.5°	463.5
45°	359.8
47.5°	281.3
50°	219.1
52.5°	171.7
55°	139.2
57.5°	117.0
60°	103.6
62.5°	100.7
65°	100.7
67.5°	97.8
70°	87.4
72.5°	75.5
75°	63.7
77.5°	50.4
80°	38.5
82.5°	28.1
85°	17.7
87.5°	7.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)