

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592717

Luminaire Tested: **HCC4W25D010MW-HM40525950-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525950-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2270.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592717
CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P592717

CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62	62	62	62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58	58	58	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55	55	55	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	334341
5°	333909
10°	327412
15°	304442
20°	261815
25°	210338
30°	164204
35°	114966
40°	59012
45°	29951
50°	15006
55°	5613
60°	2245
65°	1780
70°	1082
75°	763
80°	1137
85°	0



TEST NUMBER: P592717
 CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.0	11.2
10°-20°	658.1	29.0
20°-30°	708.9	31.2
30°-40°	465.8	20.5
40°-50°	144.8	6.4
50°-60°	28.4	1.3
60°-70°	6.0	0.3
70°-80°	2.2	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1622.0	71.5
0°-40°	2087.8	92.0
0°-60°	2261.1	99.6
0°-90°	2270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2270.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2711	
5°	2697	255
15°	2384	658
25°	1546	709
35°	764	466
45°	172	145
55°	26	28
65°	6	6
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P592717
CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2710.6
2.5°	2696.8
5°	2696.8
7.5°	2675.4
10°	2614.1
12.5°	2516.0
15°	2384.1
17.5°	2207.8
20°	1994.6
22.5°	1764.6
25°	1545.5
27.5°	1341.5
30°	1152.9
32.5°	975.1
35°	763.5
37.5°	532.0
40°	366.5
42.5°	253.0
45°	171.7
47.5°	116.5
50°	78.2
52.5°	49.1
55°	26.1
57.5°	10.7
60°	9.1
62.5°	7.7
65°	6.1
67.5°	4.6
70°	3.0
72.5°	3.0
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)