

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592718

Luminaire Tested: **HCC4W25D010MW-HM40525950-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525950-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2602.9 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592718
CATALOG NUMBER: HCC4W25D010MW-HM40525950-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P592718
 CATALOG NUMBER: HCC4W25D010MW-HM40525950-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85		
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77		
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71		
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65		
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51		
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47		
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210267
5°	213349
10°	220036
15°	235128
20°	249135
25°	246417
30°	221161
35°	172125
40°	116624
45°	72810
50°	31509
55°	10559
60°	2640
65°	1780
70°	1082
75°	763
80°	1137
85°	0



TEST NUMBER: P592718
 CATALOG NUMBER: HCC4W25D010MW-HM40525950-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.5	6.4
10°-20°	522.7	20.1
20°-30°	819.0	31.5
30°-40°	706.8	27.2
40°-50°	325.1	12.5
50°-60°	55.2	2.1
60°-70°	6.2	0.2
70°-80°	2.2	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1507.2	57.9
0°-40°	2214.0	85.1
0°-60°	2594.2	99.7
0°-90°	2602.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2602.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1705	
5°	1723	166
15°	1841	523
25°	1811	819
35°	1143	707
45°	417	325
55°	49	55
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P592718
CATALOG NUMBER: HCC4W25D010MW-HM40525950-41WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1704.7
2.5°	1704.7
5°	1723.1
7.5°	1740.0
10°	1756.8
12.5°	1792.2
15°	1841.3
17.5°	1882.7
20°	1898.0
22.5°	1875.0
25°	1810.6
27.5°	1706.3
30°	1552.8
32.5°	1359.4
35°	1143.1
37.5°	925.2
40°	724.3
42.5°	553.9
45°	417.4
47.5°	293.1
50°	164.2
52.5°	90.5
55°	49.1
57.5°	24.5
60°	10.7
62.5°	7.7
65°	6.1
67.5°	4.6
70°	3.0
72.5°	3.0
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)