

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592720

Luminaire Tested: **HCC4W25D010MW-HM40525950-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525950-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2110.5 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592720
CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P592720
 CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	185425
5°	184029
10°	179243
15°	174523
20°	166715
25°	155314
30°	136759
35°	107874
40°	78302
45°	57529
50°	46802
55°	39267
60°	35573
65°	32688
70°	30402
75°	27784
80°	25003
85°	21795



TEST NUMBER: P592720
 CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	6.6
10°-20°	383.3	18.2
20°-30°	519.7	24.6
30°-40°	445.9	21.1
40°-50°	263.3	12.5
50°-60°	166.9	7.9
60°-70°	112.1	5.3
70°-80°	61.9	2.9
80°-90°	17.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.1	49.4
0°-40°	1489.1	70.6
0°-60°	1919.2	90.9
0°-90°	2110.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2110.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1503	
5°	1486	140
15°	1367	383
25°	1141	520
35°	716	446
45°	330	263
55°	183	167
65°	112	112
75°	58	62
85°	15	17
90°	0	



TEST NUMBER: P592720
CATALOG NUMBER: HCC4W25D010MW-HM40525950-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1503.3
2.5°	1492.5
5°	1486.3
7.5°	1466.5
10°	1431.1
12.5°	1400.4
15°	1366.7
17.5°	1323.8
20°	1270.1
22.5°	1210.3
25°	1141.2
27.5°	1059.9
30°	960.2
32.5°	842.1
35°	716.4
37.5°	595.2
40°	486.3
42.5°	395.7
45°	329.8
47.5°	282.2
50°	243.9
52.5°	211.7
55°	182.6
57.5°	159.5
60°	144.2
62.5°	128.8
65°	112.0
67.5°	98.2
70°	84.3
72.5°	70.6
75°	58.3
77.5°	46.1
80°	35.2
82.5°	24.5
85°	15.4
87.5°	6.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)