

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580266

Luminaire Tested: **HCC4S30D010SL-HM43040827-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010SL-HM43040827-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2564.5 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580266
CATALOG NUMBER: HCC4S30D010SL-HM43040827-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580266
 CATALOG NUMBER: HCC4S30D010SL-HM43040827-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78				
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70				
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63				
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57				
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52				
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47				
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44				
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40				
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222750
5°	221360
10°	216655
15°	211862
20°	202064
25°	187051
30°	162695
35°	122856
40°	89058
45°	69583
50°	59506
55°	51482
60°	47414
65°	43400
70°	40572
75°	37125
80°	34806
85°	33399



TEST NUMBER: P580266

CATALOG NUMBER: HCC4S30D010SL-HM43040827-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.8	6.6
10°-20°	464.7	18.1
20°-30°	624.9	24.4
30°-40°	513.8	20.0
40°-50°	315.6	12.3
50°-60°	218.4	8.5
60°-70°	148.9	5.8
70°-80°	83.0	3.2
80°-90°	26.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.5	49.1
0°-40°	1772.3	69.1
0°-60°	2306.3	89.9
0°-90°	2564.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2564.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1806	
5°	1788	169
15°	1659	465
25°	1374	625
35°	816	514
45°	399	316
55°	239	218
65°	149	149
75°	78	83
85°	24	26
90°	0	



TEST NUMBER: P580266

CATALOG NUMBER: HCC4S30D010SL-HM43040827-41PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1805.9
2.5°	1793.2
5°	1787.8
7.5°	1767.8
10°	1729.8
12.5°	1695.3
15°	1659.1
17.5°	1606.5
20°	1539.4
22.5°	1459.6
25°	1374.4
27.5°	1271.0
30°	1142.3
32.5°	984.5
35°	815.9
37.5°	670.8
40°	553.1
42.5°	462.4
45°	398.9
47.5°	349.9
50°	310.1
52.5°	273.8
55°	239.4
57.5°	214.0
60°	192.2
62.5°	170.4
65°	148.7
67.5°	130.5
70°	112.5
72.5°	94.3
75°	77.9
77.5°	61.7
80°	49.0
82.5°	36.2
85°	23.6
87.5°	12.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)