

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580265

Luminaire Tested: **HCC4W30D010MW-HM43040827-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010MW-HM43040827-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2495.5 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580265
CATALOG NUMBER: HCC4W30D010MW-HM43040827-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580265
 CATALOG NUMBER: HCC4W30D010MW-HM43040827-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58	58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52	52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48	48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219247
5°	217608
10°	211945
15°	206371
20°	197129
25°	183649
30°	161712
35°	127539
40°	92568
45°	68013
50°	55342
55°	46407
60°	42036
65°	38642
70°	35956
75°	32836
80°	29620
85°	25757



TEST NUMBER: P580265
 CATALOG NUMBER: HCC4W30D010MW-HM43040827-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	6.6
10°-20°	453.3	18.2
20°-30°	614.5	24.6
30°-40°	527.3	21.1
40°-50°	311.3	12.5
50°-60°	197.3	7.9
60°-70°	132.5	5.3
70°-80°	73.2	2.9
80°-90°	20.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1233.5	49.4
0°-40°	1760.7	70.6
0°-60°	2269.3	90.9
0°-90°	2495.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2495.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1778	
5°	1758	166
15°	1616	453
25°	1349	614
35°	847	527
45°	390	311
55°	216	197
65°	132	133
75°	69	73
85°	18	20
90°	0	



TEST NUMBER: P580265
CATALOG NUMBER: HCC4W30D010MW-HM43040827-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1777.5
2.5°	1764.8
5°	1757.5
7.5°	1734.0
10°	1692.2
12.5°	1656.0
15°	1616.1
17.5°	1565.3
20°	1501.8
22.5°	1431.1
25°	1349.4
27.5°	1253.3
30°	1135.4
32.5°	995.8
35°	847.0
37.5°	703.8
40°	574.9
42.5°	468.0
45°	389.9
47.5°	333.8
50°	288.4
52.5°	250.3
55°	215.8
57.5°	188.6
60°	170.4
62.5°	152.4
65°	132.4
67.5°	116.1
70°	99.7
72.5°	83.5
75°	68.9
77.5°	54.4
80°	41.7
82.5°	29.0
85°	18.2
87.5°	7.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)