

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580267

Luminaire Tested: **HCC4W30D010SL-HM43040827-41WDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580267  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W30D010SL-HM43040827-41WDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2702.3 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580267  
CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580267

CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69					69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62					62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56					56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51					51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46					46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42					42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39					39			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	216028	216028	216028
5°	215516	215738	215738
10°	213010	213235	213010
15°	210457	210457	210457
20°	201815	202300	202537
25°	188766	189011	189515
30°	169147	169659	169659
35°	137326	138411	138682
40°	103630	104210	104516
45°	79369	79055	79055
50°	65416	65070	65070
55°	56149	55762	55762
60°	50078	49634	49634
65°	47106	47106	47106
70°	43818	43818	43818
75°	39746	40604	39746
80°	37363	36084	37363
85°	30852	30852	30852



TEST NUMBER: P580267  
 CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.0	6.1
10°-20°	461.8	17.1
20°-30°	634.6	23.5
30°-40°	570.6	21.1
40°-50°	360.5	13.3
50°-60°	235.4	8.7
60°-70°	159.5	5.9
70°-80°	89.8	3.3
80°-90°	25.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1261.4	46.7
0°-40°	1832.0	67.8
0°-60°	2427.8	89.8
0°-90°	2702.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2702.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1751	1751	1751	1751	1751	
5°	1741	1741	1742	1742	1742	165
15°	1648	1648	1648	1648	1648	461
25°	1387	1389	1389	1392	1392	633
35°	912	916	919	923	921	568
45°	455	453	453	453	453	361
55°	261	261	259	261	259	236
65°	161	161	161	161	161	160
75°	83	85	85	85	83	89
85°	22	22	22	22	22	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580267

CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WDW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1751.4	1751.4	1751.4	1751.4	1751.4
2.5°	1742.4	1742.4	1742.4	1742.4	1742.4
5°	1740.6	1740.6	1742.4	1742.4	1742.4
7.5°	1727.9	1729.7	1729.7	1729.7	1729.7
10°	1700.7	1700.7	1702.5	1702.5	1700.7
12.5°	1675.3	1675.3	1675.3	1677.1	1675.3
15°	1648.1	1648.1	1648.1	1648.1	1648.1
17.5°	1601.0	1602.8	1602.8	1602.8	1602.8
20°	1537.5	1541.2	1541.2	1543.0	1543.0
22.5°	1465.0	1466.9	1468.7	1470.5	1468.7
25°	1387.0	1388.8	1388.8	1392.5	1392.5
27.5°	1296.4	1298.2	1301.8	1301.8	1301.8
30°	1187.6	1189.4	1191.2	1191.2	1191.2
32.5°	1058.9	1058.9	1062.5	1064.3	1062.5
35°	912.0	915.6	919.2	922.9	921.0
37.5°	772.3	776.1	777.9	777.9	779.7
40°	643.6	647.2	647.2	650.9	649.1
42.5°	542.1	540.3	540.3	543.9	542.1
45°	455.0	453.2	453.2	453.2	453.2
47.5°	391.6	389.8	389.8	389.8	389.8
50°	340.9	339.1	339.1	339.1	339.1
52.5°	299.1	297.3	297.3	297.3	295.5
55°	261.1	261.1	259.3	261.1	259.3
57.5°	226.6	226.6	226.6	226.6	226.6
60°	203.0	201.2	201.2	201.2	201.2
62.5°	181.3	181.3	181.3	181.3	181.3
65°	161.4	161.4	161.4	161.4	161.4
67.5°	141.5	139.6	141.5	141.5	139.6
70°	121.5	119.7	121.5	121.5	121.5
72.5°	101.5	101.5	101.5	103.3	101.5
75°	83.4	85.2	85.2	85.2	83.4
77.5°	67.1	68.9	67.1	67.1	67.1
80°	52.6	50.8	50.8	50.8	52.6
82.5°	36.2	36.2	36.2	36.2	36.2
85°	21.8	21.8	21.8	21.8	21.8
87.5°	9.0	9.0	9.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)