

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580285

Luminaire Tested: **HCC4S30D010SL-HM43040830-41WDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580285  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S30D010SL-HM43040830-41WDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2923.6 lumens  
Efficiency: N/A  
Efficacy: 104.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580285  
CATALOG NUMBER: HCC4S30D010SL-HM43040830-41WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580285

CATALOG NUMBER: HCC4S30D010SL-HM43040830-41WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51																			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39																			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	233715	233715	233715
5°	233159	233395	233395
10°	230457	230695	230457
15°	227683	227683	227683
20°	218328	218853	219115
25°	204227	204486	205016
30°	182991	183546	183546
35°	148575	149764	150050
40°	112116	112760	113066
45°	85893	85526	85526
50°	70750	70386	70386
55°	60751	60321	60321
60°	54198	53705	53705
65°	50959	50959	50959
70°	47388	47388	47388
75°	42987	43940	42987
80°	40417	38997	40417
85°	33399	33399	33399



TEST NUMBER: P580285  
 CATALOG NUMBER: HCC4S30D010SL-HM43040830-41WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.5	6.1
10°-20°	499.6	17.1
20°-30°	686.5	23.5
30°-40°	617.3	21.1
40°-50°	390.0	13.3
50°-60°	254.7	8.7
60°-70°	172.5	5.9
70°-80°	97.1	3.3
80°-90°	27.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1364.7	46.7
0°-40°	1982.0	67.8
0°-60°	2626.6	89.8
0°-90°	2923.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2923.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1895	1895	1895	1895	1895	
5°	1883	1883	1885	1885	1885	178
15°	1783	1783	1783	1783	1783	499
25°	1501	1502	1502	1506	1506	685
35°	987	991	995	998	996	614
45°	492	490	490	490	490	391
55°	282	282	280	282	280	256
65°	175	175	175	175	175	173
75°	90	92	92	92	90	97
85°	24	24	24	24	24	28
90°	0	0	0	0	0	



TEST NUMBER: P580285

CATALOG NUMBER: HCC4S30D010SL-HM43040830-41WDW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1894.8	1894.8	1894.8	1894.8	1894.8
2.5°	1885.0	1885.0	1885.0	1885.0	1885.0
5°	1883.1	1883.1	1885.0	1885.0	1885.0
7.5°	1869.3	1871.4	1871.4	1871.4	1871.4
10°	1840.0	1840.0	1841.9	1841.9	1840.0
12.5°	1812.5	1812.5	1812.5	1814.4	1812.5
15°	1783.0	1783.0	1783.0	1783.0	1783.0
17.5°	1732.0	1734.0	1734.0	1734.0	1734.0
20°	1663.3	1667.3	1667.3	1669.3	1669.3
22.5°	1585.0	1586.9	1588.9	1590.8	1588.9
25°	1500.6	1502.5	1502.5	1506.4	1506.4
27.5°	1402.6	1404.5	1408.4	1408.4	1408.4
30°	1284.8	1286.8	1288.7	1288.7	1288.7
32.5°	1145.6	1145.6	1149.4	1151.5	1149.4
35°	986.7	990.6	994.6	998.4	996.5
37.5°	835.6	839.6	841.5	841.5	843.5
40°	696.3	700.3	700.3	704.2	702.2
42.5°	586.6	584.5	584.5	588.5	586.6
45°	492.4	490.3	490.3	490.3	490.3
47.5°	423.7	421.8	421.8	421.8	421.8
50°	368.7	366.8	366.8	366.8	366.8
52.5°	323.6	321.7	321.7	321.7	319.8
55°	282.5	282.5	280.5	282.5	280.5
57.5°	245.2	245.2	245.2	245.2	245.2
60°	219.7	217.7	217.7	217.7	217.7
62.5°	196.2	196.2	196.2	196.2	196.2
65°	174.6	174.6	174.6	174.6	174.6
67.5°	153.0	151.0	153.0	153.0	151.0
70°	131.4	129.5	131.4	131.4	131.4
72.5°	109.9	109.9	109.9	111.8	109.9
75°	90.2	92.2	92.2	92.2	90.2
77.5°	72.5	74.6	72.5	72.5	72.5
80°	56.9	54.9	54.9	54.9	56.9
82.5°	39.3	39.3	39.3	39.3	39.3
85°	23.6	23.6	23.6	23.6	23.6
87.5°	9.8	9.8	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)