

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580298

Luminaire Tested: **HCC4S30D010SL-HM43040835-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010SL-HM43040835-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2912.2 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580298
CATALOG NUMBER: HCC4S30D010SL-HM43040835-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580298

CATALOG NUMBER: HCC4S30D010SL-HM43040835-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95				94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89				87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83				81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77				76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72				71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59				58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56				55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	428947
5°	428394
10°	420046
15°	390573
20°	335899
25°	269839
30°	210664
35°	147505
40°	75710
45°	38428
50°	19247
55°	7183
60°	2911
65°	2306
70°	1406
75°	905
80°	1350
85°	0



TEST NUMBER: P580298
 CATALOG NUMBER: HCC4S30D010SL-HM43040835-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.1	11.2
10°-20°	844.3	29.0
20°-30°	909.5	31.2
30°-40°	597.6	20.5
40°-50°	185.8	6.4
50°-60°	36.5	1.3
60°-70°	7.8	0.3
70°-80°	2.8	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2081.0	71.5
0°-40°	2678.6	92.0
0°-60°	2900.9	99.6
0°-90°	2912.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2912.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3478	
5°	3460	327
15°	3059	844
25°	1983	910
35°	980	598
45°	220	186
55°	33	36
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P580298
CATALOG NUMBER: HCC4S30D010SL-HM43040835-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3477.6
2.5°	3459.9
5°	3459.9
7.5°	3432.4
10°	3353.7
12.5°	3227.8
15°	3058.6
17.5°	2832.4
20°	2559.0
22.5°	2264.0
25°	1982.7
27.5°	1721.1
30°	1479.1
32.5°	1251.0
35°	979.6
37.5°	682.6
40°	470.2
42.5°	324.5
45°	220.3
47.5°	149.5
50°	100.3
52.5°	62.9
55°	33.4
57.5°	13.8
60°	11.8
62.5°	9.8
65°	7.9
67.5°	5.9
70°	3.9
72.5°	3.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)