

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580302

Luminaire Tested: **HCC4W30D010MB-HM43040835-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010MB-HM43040835-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2782.4 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580302
CATALOG NUMBER: HCC4W30D010MB-HM43040835-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580302

CATALOG NUMBER: HCC4W30D010MB-HM43040835-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241671
5°	240167
10°	235066
15°	229867
20°	219220
25°	202934
30°	176510
35°	133306
40°	96610
45°	75496
50°	64552
55°	55848
60°	51460
65°	47077
70°	43962
75°	40318
80°	37718
85°	36230



TEST NUMBER: P580302
 CATALOG NUMBER: HCC4W30D010MB-HM43040835-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.2	6.6
10°-20°	504.2	18.1
20°-30°	678.0	24.4
30°-40°	557.5	20.0
40°-50°	342.4	12.3
50°-60°	236.9	8.5
60°-70°	161.5	5.8
70°-80°	90.0	3.2
80°-90°	28.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1365.4	49.1
0°-40°	1922.9	69.1
0°-60°	2502.2	89.9
0°-90°	2782.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2782.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1959	
5°	1940	183
15°	1800	504
25°	1491	678
35°	885	558
45°	433	342
55°	260	237
65°	161	162
75°	85	90
85°	26	29
90°	0	



TEST NUMBER: P580302
CATALOG NUMBER: HCC4W30D010MB-HM43040835-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1959.3
2.5°	1945.6
5°	1939.7
7.5°	1918.1
10°	1876.8
12.5°	1839.3
15°	1800.1
17.5°	1743.0
20°	1670.1
22.5°	1583.6
25°	1491.1
27.5°	1379.0
30°	1239.3
32.5°	1068.2
35°	885.3
37.5°	727.9
40°	600.0
42.5°	501.6
45°	432.8
47.5°	379.7
50°	336.4
52.5°	297.0
55°	259.7
57.5°	232.1
60°	208.6
62.5°	184.9
65°	161.3
67.5°	141.7
70°	121.9
72.5°	102.3
75°	84.6
77.5°	66.9
80°	53.1
82.5°	39.4
85°	25.6
87.5°	13.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)