

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580303

Luminaire Tested: **HCC4W30D010MB-HM43040835-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010MB-HM43040835-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2931.9 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580303
CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P580303

CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	234381	234381	234381
5°	233828	234063	234063
10°	231108	231359	231108
15°	228335	228335	228335
20°	218971	219483	219745
25°	204812	205084	205601
30°	183518	184087	184087
35°	148996	150186	150472
40°	112438	113082	113388
45°	86120	85788	85788
50°	70981	70578	70578
55°	60901	60493	60493
60°	54346	53877	53877
65°	51105	51105	51105
70°	47532	47532	47532
75°	43130	44083	43130
80°	40559	39068	40559
85°	33399	33399	33399



TEST NUMBER: P580303
 CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	6.1
10°-20°	501.0	17.1
20°-30°	688.5	23.5
30°-40°	619.1	21.1
40°-50°	391.1	13.3
50°-60°	255.4	8.7
60°-70°	173.0	5.9
70°-80°	97.4	3.3
80°-90°	27.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1368.6	46.7
0°-40°	1987.6	67.8
0°-60°	2634.1	89.8
0°-90°	2931.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2931.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1900	1900	1900	1900	1900	
5°	1888	1888	1890	1890	1890	179
15°	1788	1788	1788	1788	1788	501
25°	1505	1507	1507	1511	1511	687
35°	990	993	997	1001	999	616
45°	494	492	492	492	492	392
55°	283	283	281	283	281	256
65°	175	175	175	175	175	173
75°	90	92	92	92	90	97
85°	24	24	24	24	24	28
90°	0	0	0	0	0	



TEST NUMBER: P580303

CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1900.2	1900.2	1900.2	1900.2	1900.2
2.5°	1890.4	1890.4	1890.4	1890.4	1890.4
5°	1888.5	1888.5	1890.4	1890.4	1890.4
7.5°	1874.7	1876.7	1876.7	1876.7	1876.7
10°	1845.2	1845.2	1847.2	1847.2	1845.2
12.5°	1817.7	1817.7	1817.7	1819.6	1817.7
15°	1788.1	1788.1	1788.1	1788.1	1788.1
17.5°	1737.0	1738.9	1738.9	1738.9	1738.9
20°	1668.2	1672.1	1672.1	1674.1	1674.1
22.5°	1589.5	1591.4	1593.4	1595.3	1593.4
25°	1504.9	1506.9	1506.9	1510.7	1510.7
27.5°	1406.5	1408.5	1412.5	1412.5	1412.5
30°	1288.5	1290.4	1292.5	1292.5	1292.5
32.5°	1148.9	1148.9	1152.8	1154.7	1152.8
35°	989.5	993.4	997.4	1001.3	999.3
37.5°	838.0	841.9	844.0	844.0	845.9
40°	698.3	702.3	702.3	706.2	704.2
42.5°	588.1	586.2	586.2	590.2	588.1
45°	493.7	491.8	491.8	491.8	491.8
47.5°	424.9	422.9	422.9	422.9	422.9
50°	369.9	367.8	367.8	367.8	367.8
52.5°	324.6	322.6	322.6	322.6	320.7
55°	283.2	283.2	281.3	283.2	281.3
57.5°	245.9	245.9	245.9	245.9	245.9
60°	220.3	218.4	218.4	218.4	218.4
62.5°	196.7	196.7	196.7	196.7	196.7
65°	175.1	175.1	175.1	175.1	175.1
67.5°	153.4	151.5	153.4	153.4	151.5
70°	131.8	129.8	131.8	131.8	131.8
72.5°	110.2	110.2	110.2	112.1	110.2
75°	90.5	92.5	92.5	92.5	90.5
77.5°	72.8	74.8	72.8	72.8	72.8
80°	57.1	55.0	55.0	55.0	57.1
82.5°	39.4	39.4	39.4	39.4	39.4
85°	23.6	23.6	23.6	23.6	23.6
87.5°	9.8	9.8	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)