

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580316

Luminaire Tested: **HCC4W30D010MW-HM43040840-41NDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580316  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W30D010MW-HM43040840-41NDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3047.0 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580316  
CATALOG NUMBER: HCC4W30D010MW-HM43040840-41NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P580316  
 CATALOG NUMBER: HCC4W30D010MW-HM43040840-41NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	448805
5°	448229
10°	439484
15°	408655
20°	351440
25°	282333
30°	220420
35°	154327
40°	79188
45°	40208
50°	20129
55°	7527
60°	3034
65°	2393
70°	1479
75°	953
80°	1421
85°	0



TEST NUMBER: P580316  
 CATALOG NUMBER: HCC4W30D010MW-HM43040840-41NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	342.3	11.2
10°-20°	883.4	29.0
20°-30°	951.6	31.2
30°-40°	625.2	20.5
40°-50°	194.4	6.4
50°-60°	38.2	1.3
60°-70°	8.1	0.3
70°-80°	2.9	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2177.3	71.5
0°-40°	2802.5	92.0
0°-60°	3035.1	99.6
0°-90°	3047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3047.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3639	
5°	3620	342
15°	3200	883
25°	2074	952
35°	1025	625
45°	230	194
55°	35	38
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P580316

CATALOG NUMBER: HCC4W30D010MW-HM43040840-41NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3638.6
2.5°	3620.1
5°	3620.1
7.5°	3591.2
10°	3508.9
12.5°	3377.2
15°	3200.2
17.5°	2963.5
20°	2677.4
22.5°	2368.8
25°	2074.5
27.5°	1800.7
30°	1547.6
32.5°	1308.9
35°	1024.9
37.5°	714.1
40°	491.8
42.5°	339.5
45°	230.5
47.5°	156.5
50°	104.9
52.5°	65.9
55°	35.0
57.5°	14.4
60°	12.3
62.5°	10.3
65°	8.2
67.5°	6.2
70°	4.1
72.5°	4.1
75°	2.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)