

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580327

Luminaire Tested: **HCC4S30D010MW-HM43040927-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010MW-HM43040927-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2032.7 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580327
CATALOG NUMBER: HCC4S30D010MW-HM43040927-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580327
 CATALOG NUMBER: HCC4S30D010MW-HM43040927-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202719
5°	202911
10°	203291
15°	206269
20°	201132
25°	188698
30°	166911
35°	126906
40°	79977
45°	45912
50°	24351
55°	10107
60°	2689
65°	2277
70°	1695
75°	1525
80°	1137
85°	2264



TEST NUMBER: P580327
 CATALOG NUMBER: HCC4S30D010MW-HM43040927-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	7.7
10°-20°	452.3	22.3
20°-30°	631.2	31.1
30°-40°	519.4	25.6
40°-50°	214.0	10.5
50°-60°	48.2	2.4
60°-70°	7.7	0.4
70°-80°	2.9	0.1
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1239.4	61.0
0°-40°	1758.8	86.5
0°-60°	2020.9	99.4
0°-90°	2032.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2032.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1644	
5°	1639	156
15°	1615	452
25°	1386	631
35°	843	519
45°	263	214
55°	47	48
65°	8	8
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P580327

CATALOG NUMBER: HCC4S30D010MW-HM43040927-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1643.5
2.5°	1635.6
5°	1638.8
7.5°	1632.6
10°	1623.1
12.5°	1618.5
15°	1615.3
17.5°	1587.1
20°	1532.3
22.5°	1463.2
25°	1386.5
27.5°	1294.0
30°	1171.9
32.5°	1021.5
35°	842.8
37.5°	662.7
40°	496.7
42.5°	361.9
45°	263.2
47.5°	188.0
50°	126.9
52.5°	79.9
55°	47.0
57.5°	23.5
60°	10.9
62.5°	9.4
65°	7.8
67.5°	6.3
70°	4.7
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)