

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580348

Luminaire Tested: **HCC4W30D010BZ-HM43040930-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010BZ-HM43040930-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2334.7 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580348
CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580348
 CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76		82	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65		73	68	64		71	67	64	63
7	81	72	65	61	80	71	65	61	70	64	60		68	64	60		67	63	60	58
8	77	67	61	57	76	67	61	56	65	60	56		64	59	56		63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57	52	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302814
5°	297309
10°	281997
15°	263668
20°	239474
25°	211903
30°	176254
35°	127102
40°	79333
45°	45755
50°	25829
55°	12301
60°	7031
65°	5399
70°	3606
75°	2431
80°	2415
85°	2406



TEST NUMBER: P580348
 CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.4	9.6
10°-20°	576.0	24.7
20°-30°	708.4	30.3
30°-40°	526.1	22.5
40°-50°	213.9	9.2
50°-60°	59.2	2.5
60°-70°	18.4	0.8
70°-80°	6.2	0.3
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1508.9	64.6
0°-40°	2035.0	87.2
0°-60°	2308.2	98.9
0°-90°	2334.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2334.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2455	
5°	2401	224
15°	2065	576
25°	1557	708
35°	844	526
45°	262	214
55°	57	59
65°	18	18
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P580348
CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2455.0
2.5°	2431.4
5°	2401.2
7.5°	2340.6
10°	2251.5
12.5°	2159.0
15°	2064.8
17.5°	1952.1
20°	1824.4
22.5°	1694.9
25°	1557.0
27.5°	1407.4
30°	1237.5
32.5°	1044.2
35°	844.1
37.5°	655.8
40°	492.7
42.5°	359.8
45°	262.3
47.5°	188.4
50°	134.6
52.5°	92.5
55°	57.2
57.5°	37.0
60°	28.5
62.5°	23.6
65°	18.5
67.5°	13.4
70°	10.0
72.5°	8.5
75°	5.1
77.5°	3.4
80°	3.4
82.5°	1.7
85°	1.7
87.5°	1.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)