

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580355

Luminaire Tested: **HCC4S30D010MB-HM43040930-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010MB-HM43040930-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2314.4 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580355
CATALOG NUMBER: HCC4S30D010MB-HM43040930-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580355

CATALOG NUMBER: HCC4S30D010MB-HM43040930-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203335
5°	201821
10°	196565
15°	191392
20°	182834
25°	170325
30°	149976
35°	118278
40°	85854
45°	63076
50°	51312
55°	43052
60°	39002
65°	35840
70°	33359
75°	30501
80°	27489
85°	23776



TEST NUMBER: P580355
 CATALOG NUMBER: HCC4S30D010MB-HM43040930-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	6.6
10°-20°	420.4	18.2
20°-30°	569.9	24.6
30°-40°	489.0	21.1
40°-50°	288.7	12.5
50°-60°	183.0	7.9
60°-70°	122.9	5.3
70°-80°	67.9	2.9
80°-90°	19.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1143.9	49.4
0°-40°	1632.9	70.6
0°-60°	2104.6	90.9
0°-90°	2314.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2314.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1648	
5°	1630	154
15°	1499	420
25°	1252	570
35°	786	489
45°	362	289
55°	200	183
65°	123	123
75°	64	68
85°	17	19
90°	0	



TEST NUMBER: P580355
CATALOG NUMBER: HCC4S30D010MB-HM43040930-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1648.5
2.5°	1636.7
5°	1630.0
7.5°	1608.1
10°	1569.4
12.5°	1535.8
15°	1498.8
17.5°	1451.6
20°	1392.9
22.5°	1327.2
25°	1251.5
27.5°	1162.4
30°	1053.0
32.5°	923.5
35°	785.5
37.5°	652.7
40°	533.2
42.5°	433.9
45°	361.6
47.5°	309.5
50°	267.4
52.5°	232.1
55°	200.2
57.5°	175.0
60°	158.1
62.5°	141.3
65°	122.8
67.5°	107.6
70°	92.5
72.5°	77.4
75°	64.0
77.5°	50.4
80°	38.7
82.5°	27.0
85°	16.8
87.5°	6.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)