

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580364

Luminaire Tested: **HCC4S30D010SL-HM43040935-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010SL-HM43040935-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2831.6 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580364
CATALOG NUMBER: HCC4S30D010SL-HM43040935-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580364

CATALOG NUMBER: HCC4S30D010SL-HM43040935-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232445
5°	233568
10°	235166
15°	237529
20°	233554
25°	222818
30°	202446
35°	163301
40°	113291
45°	74380
50°	49834
55°	35461
60°	30294
65°	34819
70°	37362
75°	35981
80°	32391
85°	29861



TEST NUMBER: P580364
 CATALOG NUMBER: HCC4S30D010SL-HM43040935-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.8	6.3
10°-20°	522.5	18.5
20°-30°	746.5	26.4
30°-40°	666.9	23.6
40°-50°	342.0	12.1
50°-60°	155.5	5.5
60°-70°	115.9	4.1
70°-80°	78.9	2.8
80°-90°	23.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1448.8	51.2
0°-40°	2115.8	74.7
0°-60°	2613.3	92.3
0°-90°	2831.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2831.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1884	
5°	1886	180
15°	1860	523
25°	1637	747
35°	1084	667
45°	426	342
55°	165	155
65°	119	116
75°	76	79
85°	21	23
90°	0	



TEST NUMBER: P580364
CATALOG NUMBER: HCC4S30D010SL-HM43040935-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1884.5
2.5°	1877.6
5°	1886.4
7.5°	1886.4
10°	1877.6
12.5°	1868.8
15°	1860.1
17.5°	1833.7
20°	1779.3
22.5°	1712.6
25°	1637.2
27.5°	1542.4
30°	1421.4
32.5°	1267.0
35°	1084.5
37.5°	889.7
40°	703.6
42.5°	549.2
45°	426.4
47.5°	333.4
50°	259.7
52.5°	203.6
55°	164.9
57.5°	138.6
60°	122.8
62.5°	119.3
65°	119.3
67.5°	115.8
70°	103.6
72.5°	89.5
75°	75.5
77.5°	59.7
80°	45.6
82.5°	33.4
85°	21.1
87.5°	8.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)