

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580391

Luminaire Tested: **HCC4S30D010SL-HM43040940-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010SL-HM43040940-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2412.3 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580391
CATALOG NUMBER: HCC4S30D010SL-HM43040940-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580391
 CATALOG NUMBER: HCC4S30D010SL-HM43040940-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211932
5°	210352
10°	204881
15°	199488
20°	190553
25°	177525
30°	156314
35°	123293
40°	89493
45°	65763
50°	53480
55°	44880
60°	40655
65°	37358
70°	34766
75°	31787
80°	28626
85°	24767



TEST NUMBER: P580391
 CATALOG NUMBER: HCC4S30D010SL-HM43040940-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.2	6.6
10°-20°	438.2	18.2
20°-30°	594.0	24.6
30°-40°	509.7	21.1
40°-50°	300.9	12.5
50°-60°	190.7	7.9
60°-70°	128.1	5.3
70°-80°	70.8	2.9
80°-90°	19.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1192.3	49.4
0°-40°	1702.0	70.6
0°-60°	2193.6	90.9
0°-90°	2412.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2412.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1718	
5°	1699	160
15°	1562	438
25°	1304	594
35°	819	510
45°	377	301
55°	209	191
65°	128	128
75°	67	71
85°	18	20
90°	0	



TEST NUMBER: P580391
CATALOG NUMBER: HCC4S30D010SL-HM43040940-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1718.2
2.5°	1705.9
5°	1698.9
7.5°	1676.1
10°	1635.8
12.5°	1600.7
15°	1562.2
17.5°	1513.1
20°	1451.7
22.5°	1383.3
25°	1304.4
27.5°	1211.5
30°	1097.5
32.5°	962.5
35°	818.8
37.5°	680.3
40°	555.8
42.5°	452.3
45°	377.0
47.5°	322.6
50°	278.7
52.5°	242.0
55°	208.7
57.5°	182.3
60°	164.8
62.5°	147.3
65°	128.0
67.5°	112.2
70°	96.4
72.5°	80.7
75°	66.7
77.5°	52.6
80°	40.3
82.5°	28.1
85°	17.5
87.5°	7.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)