

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592747

Luminaire Tested: **HCC4W30D010BZ-HM43040950-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010BZ-HM43040950-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2829.6 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592747
CATALOG NUMBER: HCC4W30D010BZ-HM43040950-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P592747

CATALOG NUMBER: HCC4W30D010BZ-HM43040950-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232297
5°	233395
10°	234991
15°	237350
20°	233396
25°	222668
30°	202304
35°	163181
40°	113227
45°	74310
50°	49815
55°	35440
60°	30269
65°	34790
70°	37290
75°	35933
80°	32391
85°	29861



TEST NUMBER: P592747
 CATALOG NUMBER: HCC4W30D010BZ-HM43040950-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.6	6.3
10°-20°	522.2	18.5
20°-30°	746.0	26.4
30°-40°	666.5	23.6
40°-50°	341.8	12.1
50°-60°	155.4	5.5
60°-70°	115.8	4.1
70°-80°	78.9	2.8
80°-90°	23.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1447.8	51.2
0°-40°	2114.3	74.7
0°-60°	2611.5	92.3
0°-90°	2829.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2829.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1883	
5°	1885	180
15°	1859	522
25°	1636	746
35°	1084	666
45°	426	342
55°	165	155
65°	119	116
75°	75	79
85°	21	23
90°	0	



TEST NUMBER: P592747
CATALOG NUMBER: HCC4W30D010BZ-HM43040950-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1883.3
2.5°	1876.2
5°	1885.0
7.5°	1885.0
10°	1876.2
12.5°	1867.5
15°	1858.7
17.5°	1832.4
20°	1778.1
22.5°	1711.4
25°	1636.1
27.5°	1541.3
30°	1420.4
32.5°	1266.1
35°	1083.7
37.5°	889.0
40°	703.2
42.5°	548.9
45°	426.0
47.5°	333.2
50°	259.6
52.5°	203.4
55°	164.8
57.5°	138.5
60°	122.7
62.5°	119.2
65°	119.2
67.5°	115.7
70°	103.4
72.5°	89.5
75°	75.4
77.5°	59.7
80°	45.6
82.5°	33.3
85°	21.1
87.5°	8.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)