

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580399

Luminaire Tested: **HCC4S35D010BZ-HM43040827-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010BZ-HM43040827-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2817.3 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580399
CATALOG NUMBER: HCC4S35D010BZ-HM43040827-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580399

CATALOG NUMBER: HCC4S35D010BZ-HM43040827-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280981
5°	281250
10°	281771
15°	285900
20°	278774
25°	261551
30°	231345
35°	175919
40°	110828
45°	63652
50°	33754
55°	14021
60°	3750
65°	3181
70°	2344
75°	2097
80°	1492
85°	2972



TEST NUMBER: P580399
 CATALOG NUMBER: HCC4S35D010BZ-HM43040827-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.0	7.7
10°-20°	626.9	22.3
20°-30°	874.9	31.1
30°-40°	720.0	25.6
40°-50°	296.6	10.5
50°-60°	66.8	2.4
60°-70°	10.7	0.4
70°-80°	4.0	0.1
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1717.8	61.0
0°-40°	2437.8	86.5
0°-60°	2801.2	99.4
0°-90°	2817.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2817.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2278	
5°	2272	216
15°	2239	627
25°	1922	875
35°	1168	720
45°	365	297
55°	65	67
65°	11	11
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P580399
CATALOG NUMBER: HCC4S35D010BZ-HM43040827-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2278.0
2.5°	2267.1
5°	2271.5
7.5°	2262.7
10°	2249.7
12.5°	2243.2
15°	2238.9
17.5°	2199.8
20°	2123.8
22.5°	2028.3
25°	1921.8
27.5°	1793.7
30°	1624.3
32.5°	1415.9
35°	1168.3
37.5°	918.5
40°	688.3
42.5°	501.6
45°	364.9
47.5°	260.5
50°	175.9
52.5°	110.7
55°	65.2
57.5°	32.6
60°	15.2
62.5°	13.0
65°	10.9
67.5°	8.7
70°	6.5
72.5°	4.4
75°	4.4
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)