

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580423

Luminaire Tested: **HCC4S35D010MB-HM43040830-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MB-HM43040830-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3628.6 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580423
CATALOG NUMBER: HCC4S35D010MB-HM43040830-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P580423

CATALOG NUMBER: HCC4S35D010MB-HM43040830-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	64	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	420288
5°	428022
10°	441213
15°	436314
20°	400650
25°	345645
30°	281678
35°	208564
40°	119651
45°	57843
50°	27517
55°	9613
60°	3503
65°	2072
70°	1695
75°	1144
80°	0
85°	0



TEST NUMBER: P580423
 CATALOG NUMBER: HCC4S35D010MB-HM43040830-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.5	9.2
10°-20°	947.2	26.1
20°-30°	1156.8	31.9
30°-40°	850.4	23.4
40°-50°	281.9	7.8
50°-60°	49.8	1.4
60°-70°	7.5	0.2
70°-80°	2.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2436.5	67.1
0°-40°	3286.9	90.6
0°-60°	3618.6	99.7
0°-90°	3628.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3628.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3407	
5°	3457	332
15°	3417	947
25°	2540	1157
35°	1385	850
45°	332	282
55°	45	50
65°	7	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580423
CATALOG NUMBER: HCC4S35D010MB-HM43040830-41MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3407.4
2.5°	3409.8
5°	3456.9
7.5°	3508.6
10°	3522.7
12.5°	3489.8
15°	3416.8
17.5°	3266.3
20°	3052.3
22.5°	2803.1
25°	2539.7
27.5°	2264.6
30°	1977.7
32.5°	1690.8
35°	1385.1
37.5°	1074.7
40°	743.1
42.5°	491.5
45°	331.6
47.5°	221.1
50°	143.4
52.5°	84.6
55°	44.7
57.5°	18.8
60°	14.2
62.5°	9.4
65°	7.1
67.5°	4.7
70°	4.7
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)