

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580438

Luminaire Tested: **HCC4W35D010MB-HM43040835-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010MB-HM43040835-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3271.3 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580438
CATALOG NUMBER: HCC4W35D010MB-HM43040835-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580438
 CATALOG NUMBER: HCC4W35D010MB-HM43040835-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63		
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54		
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	424297
5°	416582
10°	395121
15°	369465
20°	335544
25°	296922
30°	246983
35°	178103
40°	111166
45°	64106
50°	36172
55°	17225
60°	9868
65°	7588
70°	5121
75°	3384
80°	3339
85°	3397



TEST NUMBER: P580438
 CATALOG NUMBER: HCC4W35D010MB-HM43040835-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	314.5	9.6
10°-20°	807.1	24.7
20°-30°	992.7	30.3
30°-40°	737.2	22.5
40°-50°	299.7	9.2
50°-60°	83.0	2.5
60°-70°	25.9	0.8
70°-80°	8.7	0.3
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2114.3	64.6
0°-40°	2851.5	87.2
0°-60°	3234.2	98.9
0°-90°	3271.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3271.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3440	
5°	3364	314
15°	2893	807
25°	2182	993
35°	1183	737
45°	368	300
55°	80	83
65°	26	26
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P580438
CATALOG NUMBER: HCC4W35D010MB-HM43040835-41NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3439.9
2.5°	3406.8
5°	3364.5
7.5°	3279.6
10°	3154.7
12.5°	3025.2
15°	2893.3
17.5°	2735.4
20°	2556.3
22.5°	2374.9
25°	2181.7
27.5°	1972.1
30°	1734.1
32.5°	1463.1
35°	1182.8
37.5°	918.9
40°	690.4
42.5°	504.2
45°	367.5
47.5°	263.9
50°	188.5
52.5°	129.6
55°	80.1
57.5°	51.8
60°	40.0
62.5°	32.9
65°	26.0
67.5°	18.9
70°	14.2
72.5°	11.8
75°	7.1
77.5°	4.7
80°	4.7
82.5°	2.4
85°	2.4
87.5°	2.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)