

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580456

Luminaire Tested: **HCC4S35D010MW-HM43040840-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MW-HM43040840-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3422.8 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580456
CATALOG NUMBER: HCC4S35D010MW-HM43040840-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580456

CATALOG NUMBER: HCC4S35D010MW-HM43040840-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76		82	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65		73	68	64		71	67	64	63
7	81	72	65	61	80	71	65	61	70	64	60		68	64	60		67	63	60	58
8	77	67	61	57	76	67	61	56	65	60	56		64	59	56		63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57	52	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443921
5°	435872
10°	413433
15°	386564
20°	351086
25°	310668
30°	258420
35°	186339
40°	116302
45°	67071
50°	37860
55°	18042
60°	10336
65°	7909
70°	5337
75°	3527
80°	3481
85°	3538



TEST NUMBER: P580456
 CATALOG NUMBER: HCC4S35D010MW-HM43040840-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.0	9.6
10°-20°	844.5	24.7
20°-30°	1038.6	30.3
30°-40°	771.4	22.5
40°-50°	313.6	9.2
50°-60°	86.8	2.5
60°-70°	27.0	0.8
70°-80°	9.1	0.3
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2212.1	64.6
0°-40°	2983.5	87.2
0°-60°	3383.9	98.9
0°-90°	3422.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3422.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3599	
5°	3520	329
15°	3027	844
25°	2283	1039
35°	1238	771
45°	384	314
55°	84	87
65°	27	27
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P580456
CATALOG NUMBER: HCC4S35D010MW-HM43040840-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3599.0
2.5°	3564.5
5°	3520.3
7.5°	3431.5
10°	3300.9
12.5°	3165.2
15°	3027.2
17.5°	2862.0
20°	2674.7
22.5°	2484.8
25°	2282.7
27.5°	2063.3
30°	1814.4
32.5°	1530.9
35°	1237.5
37.5°	961.4
40°	722.3
42.5°	527.5
45°	384.5
47.5°	276.1
50°	197.3
52.5°	135.6
55°	83.9
57.5°	54.2
60°	41.9
62.5°	34.5
65°	27.1
67.5°	19.7
70°	14.8
72.5°	12.4
75°	7.4
77.5°	4.9
80°	4.9
82.5°	2.5
85°	2.5
87.5°	2.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)