

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580465

Luminaire Tested: **HCC4S35D010MW-HM43040840-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MW-HM43040840-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3674.3 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580465
CATALOG NUMBER: HCC4S35D010MW-HM43040840-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P580465

CATALOG NUMBER: HCC4S35D010MW-HM43040840-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51																			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39																			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	293735	293735	293735
5°	293025	293334	293334
10°	289624	289938	289624
15°	286156	286156	286156
20°	274403	275059	275374
25°	256651	256992	257672
30°	229977	230689	230689
35°	186716	188206	188583
40°	140905	141710	142113
45°	107942	107506	107506
50°	88923	88462	88462
55°	76342	75804	75804
60°	68111	67519	67519
65°	64034	64034	64034
70°	59541	59541	59541
75°	54043	55235	54043
80°	50788	49012	50788
85°	41891	41891	41891



TEST NUMBER: P580465
 CATALOG NUMBER: HCC4S35D010MW-HM43040840-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.4	6.1
10°-20°	627.9	17.1
20°-30°	862.8	23.5
30°-40°	775.8	21.1
40°-50°	490.2	13.3
50°-60°	320.1	8.7
60°-70°	216.8	5.9
70°-80°	122.0	3.3
80°-90°	34.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1715.1	46.7
0°-40°	2490.9	67.8
0°-60°	3301.1	89.8
0°-90°	3674.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3674.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2381	2381	2381	2381	2381	
5°	2367	2367	2369	2369	2369	224
15°	2241	2241	2241	2241	2241	627
25°	1886	1888	1888	1893	1893	861
35°	1240	1245	1250	1255	1252	772
45°	619	616	616	616	616	491
55°	355	355	352	355	352	321
65°	219	219	219	219	219	217
75°	113	116	116	116	113	122
85°	30	30	30	30	30	35
90°	0	0	0	0	0	



TEST NUMBER: P580465

CATALOG NUMBER: HCC4S35D010MW-HM43040840-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2381.4	2381.4	2381.4	2381.4	2381.4
2.5°	2369.1	2369.1	2369.1	2369.1	2369.1
5°	2366.6	2366.6	2369.1	2369.1	2369.1
7.5°	2349.4	2351.9	2351.9	2351.9	2351.9
10°	2312.4	2312.4	2314.9	2314.9	2312.4
12.5°	2277.9	2277.9	2277.9	2280.4	2277.9
15°	2240.9	2240.9	2240.9	2240.9	2240.9
17.5°	2176.7	2179.2	2179.2	2179.2	2179.2
20°	2090.5	2095.5	2095.5	2097.9	2097.9
22.5°	1991.8	1994.3	1996.8	1999.3	1996.8
25°	1885.8	1888.3	1888.3	1893.3	1893.3
27.5°	1762.7	1765.1	1770.1	1770.1	1770.1
30°	1614.7	1617.2	1619.7	1619.7	1619.7
32.5°	1439.7	1439.7	1444.6	1447.0	1444.6
35°	1240.0	1244.9	1249.9	1254.8	1252.4
37.5°	1050.2	1055.1	1057.6	1057.6	1060.0
40°	875.1	880.1	880.1	885.0	882.6
42.5°	737.1	734.6	734.6	739.6	737.1
45°	618.8	616.3	616.3	616.3	616.3
47.5°	532.4	530.0	530.0	530.0	530.0
50°	463.4	461.0	461.0	461.0	461.0
52.5°	406.8	404.3	404.3	404.3	401.8
55°	355.0	355.0	352.5	355.0	352.5
57.5°	308.2	308.2	308.2	308.2	308.2
60°	276.1	273.7	273.7	273.7	273.7
62.5°	246.5	246.5	246.5	246.5	246.5
65°	219.4	219.4	219.4	219.4	219.4
67.5°	192.3	189.8	192.3	192.3	189.8
70°	165.1	162.8	165.1	165.1	165.1
72.5°	138.0	138.0	138.0	140.5	138.0
75°	113.4	115.9	115.9	115.9	113.4
77.5°	91.3	93.6	91.3	91.3	91.3
80°	71.5	69.0	69.0	69.0	71.5
82.5°	49.3	49.3	49.3	49.3	49.3
85°	29.6	29.6	29.6	29.6	29.6
87.5°	12.4	12.4	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)