

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592774

Luminaire Tested: **HCC4S35D010SL-HM43040850-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010SL-HM43040850-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3393.2 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592774
CATALOG NUMBER: HCC4S35D010SL-HM43040850-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P592774

CATALOG NUMBER: HCC4S35D010SL-HM43040850-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298102
5°	295873
10°	288184
15°	280588
20°	268036
25°	249710
30°	219879
35°	173420
40°	125866
45°	92487
50°	75260
55°	63116
60°	57183
65°	52564
70°	48939
75°	44655
80°	40346
85°	34815



TEST NUMBER: P592774

CATALOG NUMBER: HCC4S35D010SL-HM43040850-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.3	6.6
10°-20°	616.3	18.2
20°-30°	835.5	24.6
30°-40°	716.9	21.1
40°-50°	423.3	12.5
50°-60°	268.3	7.9
60°-70°	180.3	5.3
70°-80°	99.5	2.9
80°-90°	27.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1677.1	49.4
0°-40°	2394.0	70.6
0°-60°	3085.6	90.9
0°-90°	3393.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3393.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2417	
5°	2390	225
15°	2197	616
25°	1835	835
35°	1152	717
45°	530	423
55°	294	268
65°	180	180
75°	94	99
85°	25	28
90°	0	



TEST NUMBER: P592774

CATALOG NUMBER: HCC4S35D010SL-HM43040850-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2416.8
2.5°	2399.5
5°	2389.6
7.5°	2357.6
10°	2300.9
12.5°	2251.6
15°	2197.3
17.5°	2128.3
20°	2042.0
22.5°	1945.8
25°	1834.8
27.5°	1704.1
30°	1543.8
32.5°	1353.9
35°	1151.7
37.5°	956.9
40°	781.7
42.5°	636.3
45°	530.2
47.5°	453.8
50°	392.2
52.5°	340.3
55°	293.5
57.5°	256.5
60°	231.8
62.5°	207.2
65°	180.1
67.5°	157.8
70°	135.7
72.5°	113.4
75°	93.7
77.5°	74.0
80°	56.8
82.5°	39.5
85°	24.6
87.5°	9.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)