

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580482

Luminaire Tested: **HCC4W35D010SL-HM43040927-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580482
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010SL-HM43040927-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2654.2 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580482
CATALOG NUMBER: HCC4W35D010SL-HM43040927-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580482

CATALOG NUMBER: HCC4W35D010SL-HM43040927-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230545
5°	229098
10°	224232
15°	219268
20°	209139
25°	193584
30°	168378
35°	127162
40°	92150
45°	72008
50°	61578
55°	53267
60°	49067
65°	44917
70°	41942
75°	38459
80°	36013
85°	34532



TEST NUMBER: P580482
 CATALOG NUMBER: HCC4W35D010SL-HM43040927-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.8	6.6
10°-20°	481.0	18.1
20°-30°	646.8	24.4
30°-40°	531.8	20.0
40°-50°	326.6	12.3
50°-60°	226.0	8.5
60°-70°	154.1	5.8
70°-80°	85.9	3.2
80°-90°	27.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.5	49.1
0°-40°	1834.3	69.1
0°-60°	2386.9	89.9
0°-90°	2654.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2654.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1869	
5°	1850	175
15°	1717	481
25°	1422	647
35°	844	532
45°	413	327
55°	248	226
65°	154	154
75°	81	86
85°	24	27
90°	0	



TEST NUMBER: P580482
CATALOG NUMBER: HCC4W35D010SL-HM43040927-41PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1869.1
2.5°	1855.9
5°	1850.3
7.5°	1829.6
10°	1790.3
12.5°	1754.7
15°	1717.1
17.5°	1662.6
20°	1593.3
22.5°	1510.7
25°	1422.4
27.5°	1315.5
30°	1182.2
32.5°	1019.0
35°	844.5
37.5°	694.3
40°	572.3
42.5°	478.5
45°	412.8
47.5°	362.2
50°	320.9
52.5°	283.4
55°	247.7
57.5°	221.4
60°	198.9
62.5°	176.4
65°	153.9
67.5°	135.1
70°	116.3
72.5°	97.6
75°	80.7
77.5°	63.8
80°	50.7
82.5°	37.5
85°	24.4
87.5°	13.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)