

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580491

Luminaire Tested: **HCC4W35D010SL-HM43040930-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010SL-HM43040930-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2961.4 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580491
CATALOG NUMBER: HCC4W35D010SL-HM43040930-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P580491

CATALOG NUMBER: HCC4W35D010SL-HM43040930-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	383383
5°	375375
10°	354741
15°	331309
20°	303018
25°	270588
30°	227228
35°	159853
40°	98606
45°	59030
50°	34790
55°	17333
60°	8955
65°	5866
70°	3642
75°	2907
80°	1421
85°	2830



TEST NUMBER: P580491
 CATALOG NUMBER: HCC4W35D010SL-HM43040930-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.1	9.6
10°-20°	725.3	24.5
20°-30°	904.4	30.5
30°-40°	666.2	22.5
40°-50°	274.0	9.3
50°-60°	80.1	2.7
60°-70°	20.6	0.7
70°-80°	6.4	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1912.8	64.6
0°-40°	2579.1	87.1
0°-60°	2933.1	99.0
0°-90°	2961.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2961.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3108	
5°	3032	283
15°	2594	725
25°	1988	904
35°	1062	666
45°	338	274
55°	81	80
65°	20	21
75°	6	6
85°	2	1
90°	0	



TEST NUMBER: P580491
CATALOG NUMBER: HCC4W35D010SL-HM43040930-41MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3108.2
2.5°	3075.9
5°	3031.7
7.5°	2951.1
10°	2832.3
12.5°	2715.4
15°	2594.5
17.5°	2459.5
20°	2308.5
22.5°	2151.3
25°	1988.2
27.5°	1806.9
30°	1595.4
32.5°	1339.6
35°	1061.6
37.5°	815.8
40°	612.4
42.5°	453.2
45°	338.4
47.5°	249.8
50°	181.3
52.5°	124.9
55°	80.6
57.5°	48.3
60°	36.3
62.5°	26.2
65°	20.1
67.5°	14.0
70°	10.1
72.5°	8.1
75°	6.1
77.5°	4.0
80°	2.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)