

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580499

Luminaire Tested: **HCC4W35D010SL-HM43040930-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010SL-HM43040930-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2772.1 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580499
CATALOG NUMBER: HCC4W35D010SL-HM43040930-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580499

CATALOG NUMBER: HCC4W35D010SL-HM43040930-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243534
5°	241728
10°	235442
15°	229229
20°	218971
25°	204009
30°	179629
35°	141678
40°	102841
45°	75566
50°	61463
55°	51547
60°	46723
65°	42933
70°	39959
75°	36458
80°	32888
85°	28446



TEST NUMBER: P580499
 CATALOG NUMBER: HCC4W35D010SL-HM43040930-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	6.6
10°-20°	503.5	18.2
20°-30°	682.6	24.6
30°-40°	585.7	21.1
40°-50°	345.8	12.5
50°-60°	219.1	7.9
60°-70°	147.2	5.3
70°-80°	81.3	2.9
80°-90°	22.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.1	49.4
0°-40°	1955.8	70.6
0°-60°	2520.8	90.9
0°-90°	2772.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2772.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1974	
5°	1952	184
15°	1795	504
25°	1499	683
35°	941	586
45°	433	346
55°	240	219
65°	147	147
75°	76	81
85°	20	23
90°	0	



TEST NUMBER: P580499

CATALOG NUMBER: HCC4W35D010SL-HM43040930-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1974.4
2.5°	1960.4
5°	1952.3
7.5°	1926.1
10°	1879.8
12.5°	1839.4
15°	1795.1
17.5°	1738.7
20°	1668.2
22.5°	1589.7
25°	1499.0
27.5°	1392.2
30°	1261.2
32.5°	1106.1
35°	940.9
37.5°	781.7
40°	638.7
42.5°	519.8
45°	433.2
47.5°	370.7
50°	320.3
52.5°	278.1
55°	239.7
57.5°	209.5
60°	189.4
62.5°	169.3
65°	147.1
67.5°	128.9
70°	110.8
72.5°	92.7
75°	76.5
77.5°	60.5
80°	46.3
82.5°	32.3
85°	20.1
87.5°	8.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)